

ClickShare Wireless Speakerphone

ClickShare Wireless Speakerphone, Ultra-Long-Distance Pickup Beyond 3 Meters



- **Flexible expansion, supports multiple cascading connections**
- **Precision audio pickup, capturing every spoken word with exceptional clarity**
- **AI-driven noise reduction, intelligently filtering out over 300 types of background noise, ensuring meetings stay focused on communication**
- **AI-powered volume optimization, enhancing the speaker's voice while minimizing background distractions**
- **Smart spatial audio: Enables clear voice pickup even in large**

The ClickShare Wireless Speakerphone seamlessly integrates with ClickShare X-Display, featuring plug-and-play functionality with no complex setup required. It effortlessly extends the microphone pickup range within the meeting space, making it ideal for medium-to-large conference rooms exceeding 12 meters, effectively enhancing audio coverage and communication clarity.

Product specifications**CLICKSHARE WIRELESS SPEAKERPHONE**

Microphone	
Mic quantity	8 beamforming MEMS microphones
Pickup Distance	4m
Sensitivity	-35dB±1dB
Frequency response	100012Khz
Sampling rate	48Khz
Echo cancellation	Yes
Noise suppression	Yes
Automatic gain control	Yes
Speaker	
Speaker Quantity	1
Output Power	4w
THD	1kHz1%1W
Power	
Power Supply	DC 54V
PowerCord	China, length 1.5Meters
Max Operating Power Consumption	< 8W
General specifications	
Key	1*Mute1*Vol+1*Vol-
Light	1*Mute1*Vol+1*Vol-1*Wired Connection1*Wireless Connection
Cascade number	4
Language	Chinese/English
Connections	
Ports	2*RJ451*USB-C1*DC1*Power
Connected type	RJ45/USB-C/Wireless USB Dongle
Accessories	
Power Cable	1
USB Cable	1 (USB-C to USB-A)
RJ45 Cable	1
USB Dongle	1
Storage Box	Yes
Environment	
Operation Temperature	0°C~40°C
Operation Humidity	10% ~ 90% RH
Storage Temperature	-20°C~60°C
Storage Humidity	10% ~ 90% RH
Altitude	0 5000metres

Last updated: 29 May 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.