

# PanoramaShare

Bundle of CRPN-62B with ClickShare set



Meetings are all about collaboration. That's why Barco bundles its two meeting room collaboration products par excellence – ClickShare and the CRPN-62B panorama projector – as a highly attractive system. The Panoramashare bundle provides your teams with the perfect tools to share multiple screens in the most comfortable setup possible.

## Optimal collaboration

With its exceptionally wide 21:9 aspect ratio, panoramic image and 2,560 x 1,080 native resolution, the CRPN-62B is the ideal alternative for the standard configuration with two separate LCD panels or two projectors that are blended into one picture. ClickShare, Barco's wireless meeting room collaboration system, fully benefits from this expanded canvas to display the users' images in a side-by-side manner. In this way, ClickShare optimally uses the projector's pixel estate to offer the most comfortably viewing conditions possible.

## All needed components

Next to the ClickShare set and the CRPN-62B, the PanoramaShare bundle contains all other additional elements to connect the system. This not only includes the cables, but also the intelligent cross-link device that produces the 21:9 picture format.

**Product specifications****PANORAMASHARE****CRPN-62B names**

Projector type	Panorama, single chip DLP projector
Technology	LVDC DMD™ with DarkChip3™
Resolution	2,560 x 1,080 (Panorama)
Brightness	5,500 lumens
Contrast ratio	6,500:1
Brightness uniformity	>90%
Aspect ratio	21:9 (2,37:1) Panorama
Lenses	0.8:1 EN42 wide angle lens 0.8-1.21:1 EN46 ultra wide zoom lens 1.2-1.7:1 EN43 wide angle lens 1.7-2.5:1 EN41 standard zoom
Optical lens shift	Vertical: -222% to +222% Horizontal: -78% to +78% on zoom lenses
Color correction	RealColor™
Lamps	2 x 300W UHP Vidi
Inputs	2 x DVI-I; 2 x HDMI 1.3a; 2 x VGA; Video inputs; 1 x component; 1 x S-video
Optional Inputs	2 x HDMI 1.4 via X-port 2 x 3GSDI via X-port
Input resolutions	Up to 2,560 x 1,600 pixels input on all models. Output resolution depends on native resolution; HDTV (1080p, 1080i, 720p); EDTV (576p, 480p); SDTV (576i, 480i); NTSC, PAL, SECAM; progressive scan
Control	1 x RJ-45 TCP/IP; 1 x 9-pin D-SUB RS232; 2 x 12V programmable trigger (3.5mm mini jack); 1 x Wired Remote 3.5mm mini jack; 2 x USB
Network connection	10/100 base-T, RJ-45 connection
Dimensions (WxLxH)	510 x 233 x 376 mm 20.08 x 9.17 x 14.80 inches
Weight	12.7 kg (28.0 lbs)

**ClickShare specs**

Video outputs	DisplayPort, Single link DVI-I VGA (via included convertor, highest resolutions only with reduced blanking) In "Dual screen" mode, connection can occur either through DVI and DisplayPort, or through VGA and DisplayPort.
Number of sources simultaneous on screen	4
Number of simultaneous connections	25
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Band	2.4 GHz and 5 GHz

Last updated: 04 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.