

# MFCD 2320

20" Medical Flat Color Display



## 技术规格

## MFCD 2320

一般规格	
技术	<ul style="list-style-type: none"><li>TFT AMLCD VA Mode LCD</li><li>Color</li></ul>
自然分辨率	1600 x 1200 / 1200 x 1600
像素间距	0.255 mm
屏幕对角线距离	510 mm (20.1")
可视区域尺寸	408 x 306 mm (16.1 x 12")
视角	170° (at 10:1 contrast)
暗室对比度	350:1 typical
亮度	native 180 Cd/m <sup>2</sup> (52.8 fL)
稳定性, 校正和自动化质量控制	Embedded, patent-pending I-Guard®
数字视频输入	DVI (complying to DVI 1.0)
模拟视频输入	<ul style="list-style-type: none"><li>VGA D-SUB15 connector</li><li>BNC (monochrome only)</li></ul>
演示控制及交互行为	<ul style="list-style-type: none"><li>DDC (complying to DDC2Bi standard)</li><li>EDID</li></ul>
数字化视频/DDC输入连接器	One physical DVI connector, one cable
USB	USB-hub with 1 up-and 2 down stream ports
支持分辨率	<ul style="list-style-type: none"><li>1600 x 1200 (Landscape)</li><li>1200 x 1600 (Portrait)</li><li>VGA boot</li></ul>
输入电源	<ul style="list-style-type: none"><li>90 to 264 VAC</li><li>45 to 65Hz</li><li>70W max</li></ul>
节电	Supports DPMS
操作温度范围	0°C to +40°C (32°F to 104°F)
标准参数内	+15°C to +35°C (59°F to 95°F)
安全	<ul style="list-style-type: none"><li>CE</li><li>UL60950</li><li>CSA C22.2 No 60590 (c-UL)</li><li>CB</li><li>IEC 60950</li><li>DEMKO EN 60950</li></ul>
散发	EN 55022
免疫性	EN 50082-1
医疗	FDA 510k (Please contact factory for status)
尺寸	<ul style="list-style-type: none"><li>L: 525 x 485 x 250 mm</li><li>P: 385 x 585 x 250 (15.2 x 23.0 x 8.8")</li></ul>
净重	13.9 kg (30.6 lbs)
人体工程学	<ul style="list-style-type: none"><li>Tilt &amp; swivel base with P/L rotation</li><li>100mm VESA mounting standard</li><li>AR coated front cover</li></ul>
演示控制	<ul style="list-style-type: none"><li>Display on/off</li><li>Backlight adjustment</li><li>OSD</li></ul>

生成于: 16 Mar 2023

技术规格随时变化, 不会事先通知。请访问[www.barco.com.cn](http://www.barco.com.cn), 获取更新信息。