

BARCOData 3200



技术规格**BARCODATA 3200****一般规格**

对比度	5x4 Checkerboard: 150:1 Full Field Contrast: 300:1
深度	662 mm / 26 inch
高度	372 mm / 15 inch
输入	Communication: 1 D9-female Stereo Audio: 2 x Cinch (RCA) RGB trilevel sync, sync on green or sync separate: 5 x BNC (Optional) RGB analog standard sync, sync on green or sync separate: 5 x BNC (Optional) Component Video: 4 x BNC (Optional) Video/S-Video: 1 x BNC/4-pin DIN (Optional) RS232 loop-through: 1 x D9-female
光输出	ANSI Normal: 1200 Lumen Full White: 1450 Lumen Equivalent CRT Peak White: 5000 Lumen
输出	RS232 loop-through: 1 x D9-male Stereo Audio: 2 x Cinch (RCA)
分辨率	True LCD Panel Resolution 720 x 480 Maximum Display Resolution 800 x 600
屏幕尺寸	Minimum Screen Width 1m Maximum Screen Width 10m
净重	Net weight 45 kg / 99 lbs Shipping weight 57 kg / 126 lbs
宽度	633 mm / 25 inch

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。