


SLM R8 Executive



技术规格

SLM R8 EXECUTIVE

| 一般规格 | |
|-----------|--|
| 光输出 | 8000 ANSI lumens |
| 数字微镜器件 | three S-XGA DMDs (1280 x 1024) |
| 亮度均匀性 | 亮度一致性: >总屏幕的90% |
| 分辨率 | 1280 x 1024 (native) |
| 灯泡 | 2.0 kW Xenon illumination system Typical lifetime: 500 hours Max. lifetime: 1000 hours |
| 对比度 | >800:1 (全白/全黑) 高对比度模式: >1600:1 |
| 屏幕宽度 | 5米-15米/ 6英尺-50英尺 |
| 兼容性 | All video sources in Composite, S-VHS, Component or RGB formats or serial digital format All currently proposed HDTV, extended and improved television standards Most Macintosh computers Computers and electronic workstations with a resolution up to 1600 x 1200 pixels Two digital input slots allow direct digital interfacing with current and future digital inputs |
| 镜头 | Fixed focal length lenses are available with a throw ratio of 0.8:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 1.2:1 (long throw). Motorized Zoom Lenses with a throw distance of 1.6-2.0,2.0-2.8,2.8-5.0,5.0-8.0 times the screen width |
| 输入 | 2 x multifunctional 5-Cables input (high bandwidth) for the connection of: -RGB analog signals with standard sync (BNC) or tri-level sync, sync on green or separate sync -Standard video signals -S-VHS signals 2 x DVI in + 1 x DVI out SDI loop-through (Serial Digital Input) Video input |
| 可选 | SDI loop-through (Serial Digital Input) HD-SDI loop-through (High Definition Serial Digital Input) Network card |
| 通信 | 1 x D9 connector for RS232 or RS422 loop-through 1 x D9 connector for peripherals 1 x 3-pin male XLR connector for wired remote network connection |
| 特殊性能 | Linked Constant Light Output balances the brightness of 'linked' SLM Executive projectors True Seamless Switching and cross-fade effects Click-and-Play  fast-swap lenses Built-in light shutter Optional edge-blending software ScenergiX |
| 噪音级别 | < 54 dBA |
| 功率消耗 | 2550 W |
| 电源 | 230 V (公差180 V -255 V) |
| 安全级别 | Compliant with UL1950 and IEC950 |
| 电磁干扰 | BARCO's SLM Executive Series complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A |
| 净重 | 45 kg (99 lbs) |
| 网络连接 | Optional |
| 特性 | · Picture-in-picture · Seamless source switching with effects |
| 尺寸(宽x长x高) | 529 x 795 x 429 mm (20.8 x 31.3 x 16.9 inch) |
| 镜头移动 | TLD Lenses Motorized V shift: -20% +100% Motorized H shift: max. 65% (L+R) For specific details per lens type: see lens product pages |
| ScenergiX | Standard |
| 封装DLP™内核 | Not available |
| 无缝切换 | Standard |

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。