


# OverView MVL-6715

Industry-standard 67" SXGA+ 4:3 LED video wall



The OverView MVL-6715 is an easy to operate 4:3 LED-lit projection module that has been designed to offer the typical detail and brightness needs in SXGA+ resolution for control rooms where space is not a constraint.

### Unmatched LED lifetime

Barco's unique liquid cooling system significantly reduces the temperature of the LEDs. This not only prolongs the lifetime of the LEDs (>80,000 hrs), but also allows for durably higher brightness levels. The long LED lifetime guarantees a great uptime and very low overhead costs. The use of LEDs as a light source, also results in low power consumption.

### Comfortable viewing experience

To ensure good wall uniformity in terms of color and brightness levels, the OverView MVL-6715 comes with Barco's Sense<sup>5</sup> automatic calibration system. This system works with an advanced color sensor that continuously measures the primary color levels of the entire wall, and adjusts white point and color when needed. This results in a significantly more accurate cube to cube uniformity, over the complete runtime. Furthermore, the module's robust structure makes the OverView MVL-6715 suitable for use in industrial environments.

### Key characteristics

- 6x redundancy of LEDs (per color)
- 3rd generation LEDs for unmatched brightness & minimal power consumption
- Sense<sup>5</sup> automatic white point and primary colors calibration, for brightness and color stability
- Active liquid cooling ensures longer LED lifetime
- Wide color gamut
- Less disposables, less waste
- 4:3 aspect ratio, 16:9 version becomes available during 2013

## Product specifications

## OVERVIEW MVL-6715

### General specifications

Resolution	1400x1050
Brightness	on-screen: 305 Cd/m <sup>2</sup>
On-screen contrast	1,200,000:1 (dynamic)
Display technology	DLP rear projection
Color gamut	EBU
White point	6500k
Screen	WV-FEL
Color stability	Self calibration with Sense <sup>5</sup> based on advanced color sensor
Dimensions	<ul style="list-style-type: none"><li>■ Diagonal: 67"</li><li>■ Width: 1364 mm   53.7"</li><li>■ Height: 1023 mm   40.3"</li><li>■ Depth: 942 mm   37.1"</li></ul>
Light source	Light source 6x redundancy for each of 3 LEDs
Light source lifetime	> 60,000h (typ.) > 80,000h (eco) MTBF LED: > 500,000h
Conditions for operation	10°C-40°C, 80% humidity (nc)
Input voltage	90 – 240 V, 50-60Hz
Power	150W (eco) 200W (typ.) 270W (max)
Heat dissipation	510 BTU/h (eco) 680 BTU/h (typ.) 920 BTU/h (max)
Signal input/output	Dual link DVI in / Dual link DVI out
Pixel clock	320 MHz
Input frequency	24 – 62 Hz
Genlock	49 – 61 Hz
Signal processing	Loop through Cropping / upscaling
Direct ethernet access	Built-in web server
Graphical user interface	All settings and operational parameters
Integration to third party equipment	WEB service API (optional)
Warranty	2 years
Brightness uniformity	>95%
Screen gap	< 1.5 mm   0.06" (@25°C) < 0.4 mm   0.015" (@30°C)
Weight	80.5 kg   177.5 lbs (projection module) and 21 kg   46.3 lbs (pedestal)
Signal connection	Loop through
Third party interface	WEB service API (optional)

Last updated: 04 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.