

NGS-D200 Pro3D

Compact, 4+ megapixel, 3D stereo encoder & decoder



The Barco NGS-D200 Pro 3D encoder and decoder provides the highest quality visual experience for collaborators. This encoder/decoder supports 3D stereo and up to 4 megapixel video and graphics sources with audio over any IP network environment.

Using the high performance Video-to-Data (V2D) codec, the NGS-D200 accurately captures and streams content from point-to-multipoint with low latency, thus increasing communication and cohesion among global teams. Integrated keyboard and mouse control with encoding and decoding functionality in a single unit creates a seamless environment for application sharing, simulation and training needs.

Key features

- High resolution support: Dual link DVI-I input capable of streaming video and graphics of over 4 million pixels over any network
- Visually lossless codec: Compress high resolution graphics ensuring pixel-perfect delivery regardless of available bandwidth, while using 4:4:4 color space conversion
- Application programming interface (API): Allow integration of the NGS-D200 and recording/playback functionality in the workflow via the BCS management system API
- Passive video loop-through: Ensures a reliable video source without power
- 3D Stereoscopic support: Stream and manipulate remote 3D graphics and animations
- Redundant LAN: Failover protection to maintain network connectivity with zero downtime
- Configurable modes: Switch between encoding and decoding in a single unit

Product specificaties

NGS-D200 PRO3D

General specifications

Aantal kanalen	1 video channel
USB-poorten	2xType A for KB/M; 1xType B towards host PC
Audio-ingangen, uitgangen	3.5 mm locking stereo jack audio line in-out (rear), 3.5 mm mic & headphone (front)
Audiokanalen	Stereo/mono
Audioformaat	Pulse code modulation (PCM)
Sync	Hardwired end-to-end; Timestamp NTP
Netwerk	2x1000 Base T RJ 45 (redundant LAN)
Netwerkprotocol	IPv4; Unicast-multicast (IGMP version 2)
Opslag apparaatconfiguratie	Removable SD Card
QoS/foutenverberging	Advanced mechanisms to cope with packet loss, network latency, and jitter that are fully configurable on the fly
Beheerinterface	Managed mode – Admin/Client interface, Web Endpoint Controller Standalone mode – Web interface
Voeding	External, locking adapter 110/220 V AC, 60/50 Hz, 40W (136 BTU's/hr), auto switchable
Rackmontage	Optional rack mount equipment available
Afmetingen (B x D x H)	186.9mm x 121.92mm x 41.15mm / 7.37" x 4.8" x 1.62"
Gewicht	1.6 kg / 3.6 lbs
Afmetingen verpakt (B x H x D)	382mm x 273mm x 85mm 15,04" x 10,75" x 3,35"
Gewicht in verpakking	2.0 kg / 4.40 lbs
Bereik bedrijfstemperatuur	0-40°C, 32-104F
Video	Tx – Passive loopback of local input signal Rx – Passive loopback of local input signal, signal from remote source, PIP (with scaling, alpha and chroma control)
Audio	Tx/Rx – Local audio input; signal from remote source; mix of both with mixing level control
Codec	Proprietary V2D (Video-to-Data) with 4:4:4 and 4:2:2 color sampling and real-time compression tuning Software decodable
Toetsenbord & muis	Secure remote keyboard and mouse HID support over IP Supported layouts: <ul style="list-style-type: none">■ QWERTY (US, UK, NL, IT, SP, PO)■ AZERTY (FR, BE-comma, BE-dot)■ QWERTZ (DE-T1)■ Chinese Simplified■ Russian
Kenmerken videoboard	On-the-fly switching between Tx & Rx
Certificeringen en conformiteit	Safety: UL/CSA/EN/IEC 60950-1 CB report EMC: CE, FCC Part 15 Class A, CISPR 22, ICES-003, CCC
NGS-D200 Pro3D	
Video-ingangen, uitgangen per kanaal	Dual-link DVI-I in / Dual-link DVI-D out
Resolutiebereik	800x600 (min) to 2560x1600@60Hz or 3840x2160@30Hz (max)
Coderingssnelheid (afhankelijk van resolutie)	60fps: 800x600, 1280x720, 1280x720, 1280x1024, 1600x1200, 1920x1080, 1920x1200 30fps: 2560x1600 15fps: 3840x2160
Pixelklok	DVI – 330 MHz Analog – 170MHz
3D-mogelijkheid	Yes

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.