


V9m

9mm pixel pitch, 4,000 nits LED display



- **Lightweight and slim**
- **Available in transparent version**
- **Unique magnetic lock for quick installation**

With the lightweight V9m LED display, rental companies have the flexibility to build large dynamic video backdrops for both indoor and outdoor stages, whether straight or curved, as well as side screens on lightweight trusses. What's more, the V9m is also ideally suited for overhead and ceiling screens and is available as transparent LED display as well.

Quick and easy to install

The V9m comes with a special magnetic V-lock™, for reduced setup times and safe installation by one single person. A lightweight and slim LED display, the V9m can be boxed and shipped easily. Just like its V14m brother, the V9m shares its mechanics with the C series, so that rental companies that already own the Barco C series mechanics can reuse them.

Suited for outdoor stages

The V9m can both be used indoors and outdoors, as it is equipped with the latest outdoor SMD technology. Moreover, it's rated IP65 which guarantees that it's fully waterproof.

High-performance scaling and control

Just like the other V LED displays, the V9m is driven by the DV-100 image processor, which offers high-performance scaling and supports all the latest video standards (HDMI, DisplayPort, 3G SDI). In combination with the V series Toolset (VTS), the DV-100 allows for creative setups and remote control.

Product specificaties

V9M

General specifications	
Doorzichtigheid	5% (transparent shader) 0% (non-transparent shader)
Helderheid	4,000 nits
Led-type	3-in-1 SMD
Pixeldichtheid	11,025/sqm 1,024/sqft 7,056/tile
Kijkhoek	H: 120 degrees V: -60/+60 degrees (transparent shader) V: -45/+60 degrees (non-transparent shader)
Contrastverhouding	4,000:1 (transparent shader) 5,000:1 (non-transparent shader)
Pixelpitch	9.52 mm
Levensduur	50,000 hrs (@50 % brightness)
Energieverbruik	516 W/sqm max. 206 W/sqm typical
Netspanning bij gebruik	200 -240V / 50 -60 Hz
Paneelgrootte (B x H x D) in mm	800 x 800 x 109 (31.5 x 31.5 x 4.3 inch)
Gewicht	13.5 kg/tile 29.8 lbs
IP-classificatie	IP65
Verwerking	16 bit/color
Vernieuwingssnelheid	Over 2,800 Hz
Onderhoudsgemak	back
Bedienbare digitizer	DV-100
Certificeringen	CE, ETL, FCC Class A, TÜV, RoHS, WEEE

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

