

# OverView OSV-350F

High brightness seamless flat 5 megapixels collaboration video wall



The OverView OSV-350F is a high-performing video wall that boosts high brightness levels. Featuring a large, flat, seamless canvas, a mix of data and video can be displayed simultaneously in high quality without the interruption of a seam or a bezel. The display's flat set-up, combined with the absence of a rear maintenance area, ensure that a minimum of real estate space is used.

Furthermore, benefiting from advanced signal processing, the OSV offers a feature-rich solution with high image quality and excellent reliability. Compact in setup, this video wall suits a multitude of possible applications from crisis operations and war rooms, to brainstorm and planning rooms, and of more traditional control room applications in utilities, energy and process control.

## **Laser-phosphor projection for high brightness**

Images are displayed on the OSV HB series using state-of-the-art laser-phosphor projection technology. This highly increases the system's brightness levels, allowing it to be used in environments with challenging lighting conditions. Additionally, this HB series has a higher resolution than its LL counterpart, offering 5 megapixels to display data. The OSV-350F consists of three blended rear-projection cubes, forming one seamless image.

## **A real seamless canvas**

No matter how thin, seams and bezels are always a nuisance. Especially when displaying numbers or other critical content, any interruption is too much. OSV's Seamless canvas makes sure a wealth of different sources can be positioned anywhere on the screen, in the most efficient way.

## **Saving real estate space**

Compared with conventional rear-projection systems, the OSV video walls have a limited depth of less than 1.2 meters/47 inches. In this way, the available real estate space is used to its maximum.

### **High brightness**

The OSV HB series is equipped with laser-phosphor projection technology, strongly boosting its brightness levels. This allows the system to be used in environments with challenging lighting conditions.

### **Free from image retention**

The OSV uses DLP technology, which is not sensitive to image retention. This means you can show static images without risking burn-in effects.

### **Enhanced immersive user participation**

The use of a curved screen creates an immersive effect that makes everyone in the room feel more involved, which improves the collaboration.

### **More pixels**

Compared with the OSV LL series, the OSV HB series has a 30% higher resolution. This means that even more information can be displayed on the seamless canvas.

### **Real-life collaboration**

The large screen area, gives all participants in a telepresence meeting a front row seat. Using 3, 5 or 7 rear-projection modules, the horizontal size of the OSV system varies from 3.5 to 6.5 meters (120 to 240 inches).

## Product specificaties

## OVERVIEW OSV-350F

General specifications	
Resolutie	5 Mega Pixels
Pixelgrootte	0.88 mm   0.035"
Helderheid	230 Nit (cd/m <sup>2</sup> )
Systeemcontrast	50:1 with 100 lux ambient light on-screen
Kleur	95% REC709
Weergavetechnologie	Rear projection DLP
Wit punt	2,300K   6,500K   9,300K   arbitrary
Helderheidsuniformiteit	85% ANSI 9
Schermbreedte	Barco 6mm Rigid Seamless Rear Projection Screen
Ruimte tussen schermen	None. No seams or bezels
Schermafmating	2735 (length) x 1400 (height) mm 108 (length) x 55 (height) inch
Radius	N/A -flat screen
H / V Half Gain-hoek	60° both horizontal and vertical
Schermschijfreflectiviteit	2%
Afmetingen (fysiek)	3539 (length) x 2370 (height) mm 139 (length) x 93.3 (height) inch
Beginhoogte beeld	750 mm / 29.5 inch above floor
Diepte	Center: 1170 mm / 46 inch
Gewicht	585 kg / 1290 lbs
Lichtbron	Laser phosphor illumination
Levensduur lichtbron	20,000 h (normal mode)
Aanbevolen onderhoudsinterval	3 / year No burn-in, no image retention
Gebruiksomstandigheden	0°C-35°C, 32°F-95°F 80% humidity (non condensing)
Ingangsspanning (wisselstroom)	110 – 240 V, 50-60 Hz
Vermogen	Typical : 1250 W ; Maximum : 1600 W
Warmteafvoer	Typical : 4270 BTU/h ; Maximum : 5465 BTU/h
Signaalingangen	Twin dual link DVI-D
Ingangsfrequentie	300 MHz
Garantie	2 years

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.