

S70

Stand-alone 70" display for monitoring, control or collaboration with SXGA resolution and multiple input capabilities.



Product specificaties**S70****General specifications**

Wisselstroom	95-230 VAC $\pm$ 10%, 50-60 Hz
Helderheidsuniformiteit	> 95%
Communicatie	• 2 x D9 connectors for RS232 in/out • 1 x D9 connector for Com 800 • 1 x Mouse Out (DIN 13) • 1 x Mini-jack for wired RC • 1 x IR receivers
Compatibiliteit	• All current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, S-VHS, RGB or component forms • All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV ...) • All computer graphics formats from VGA, SVGA, XGA to SXGA • Most Macintosh computers • Electronic workstations with a resolution up to 2,000x1,280 pixels at 76 Hz • Most sources with a pixel clock up to 200 MHz
Contrast	350:1
Diepte	The unit is 797 mm deep and has a footprint of 603 mm
Naleving van milieuwetgeving	Ambient temperature 0-40°C 30-105°F at max. 80% humidity (non condensing)
Hoogte	1952 mm
Hoogte met wielen	2003 mm
Ingangen	• 1 x 5 BNC for: RGB, component video, composite video, S-video • 1 x S-video (4-pin mini-DIN) • 1 x Video (BNC or cinch) • 1 x VGA (D15) connector • 3 x Stereo audio L/R (cinch) Optional: • 1 x Serial Digital Input/Output SDI/SDO • 1 x IEEE1394 FireWire
Lamp	100 Watts perfectly pre-aligned UHP™ lamp with an operation time of 8000 hours
Lcd-panelen	3 active matrix Poly-Silicon LCD panels (1.8" diagonal), with a resolution of 1,280x1,024 at 24 bit/pixel for 16.7 million colors
Lichtuitvoer	Brightness: 110 cd/m ² or 500 lumens
Uitgangen	• 1 x VGA (D15) connector • 1 x Stereo audio L/R (cinch) • 1 x Trigger Output Mini-jack
Energieverbruik	Typ. 220 Watts
Afstandsbediening	All controls are accessible through a soft-touch panel or a new user-friendly backlit IR remote control: • Source switching • User settings per source • Installation/Service adjustments
Scanfrequenties	Horizontal: 15 kHz-115 kHz Vertical: 25 Hz-150 Hz
Schermmaat	The screen has an all around visibility. It is the Fresnel lens that provides the evenness of image brightness. Two or more S70 displays can be lined up side by side with a seam of less than 2 mm.
Schermbreedte (min./max.)	1360 mm x 1088 mm 53.5 in. x 42.8 in.
Speciale functies	• Cabling, operation and servicing (front access) • Available on wheels or with adjustable feet • In case of adjustable feet, height of support on customer's request • Built-in 2x3 Watt stereo audio amplifier • Color temperature adjustment (broadcast 3200°K, film 5400°K, video 6500°K, computer 9500°K or custom) • Fits through regular doors • Autostart function
Gewicht	total weight 149 kg 348.33 lbs
Breedte	1552 mm

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.