

iQ Pro G300



Especificaciones del producto

IQ PRO G300

Especificaciones generales	
Salida de luz	3,500 ANSI lumen
brillo uniforme	>95 % for the total screen
relación de contraste	>400 : 1 (full white/full black)
Paneles LCD	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3).
resolución	1024 x 768 (native)
Red	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor - Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... ■ RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) ■ 4 USB connectors ■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
características	■ Advanced picture-in-picture ■ Seamless switching with effects ■ Standard cable basket ■ Standard light shutter ■ Advanced digital zoom
compatibilidad	The iQ Pro G300 is compatible with: ■ All current video sources (PAL,SECAM, NTSC) in Composite, S-VHS, Component or RGB formats ■ All currently proposed HDTV, extended and improved television standards (1080i, 720p) ■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA ■ Most Macintosh computers ■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz ■ Most computer sources with a pixel clock up to 160 MHz ■ DVI sources up to SXGA
tamaño de pantalla	From 1-6 m/3-20 ft.
entradas	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGBS. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
lámpara	2x 200 Watt UHP lamp, in lamp housing Typical lifetime: 1500 h/lamp. 1500 hours in Dual Lamp Mode or max. 3000 hours/set in Single Lamp Mode.
lentes	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6, 3.0-6.0 times the screen width
frecuencias de barrido	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
desplazamiento de lente	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
dimensiones (ancho x largo x alto)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
peso	Net weight, body only: 12.9kg/28.5 lbs.
comunicación	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
nivel de ruido	
corriente alterna	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
consumo de potencia	Max 550 Watt
disipación de potencia	Max 1878 BTU/h
regulación de seguridad	Compliant with UL1950 and EN60950
interferencia electromagnética	BARCO's iQ Pro G300 complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
Conmutación fluida	Standard

Generado en: 09 Jul 2024

© 2024 Barco nv. Todos los derechos reservados. Prohibida la reproducción total o parcial sin autorización por escrito. Todos los nombres de marcas y de productos son marcas comerciales, marcas comerciales registradas o nombres comerciales de sus respectivos titulares. Debido a la innovación continua, la información y las especificaciones técnicas están sujetas a cambios sin previa notificación. Consulta www.barco.com para ver las especificaciones más recientes.

