

# ScreenPro PLUS 1600

ScreenPro PLUS™ is a fully integrated presentation system that simplifies system interconnections, setup and control while supporting advanced features for presentations with



一般规格

用户控制

- Up to six screen control
- Complete integrated control of system setup functions
- Joystick simplifies visual setup of inputs
- Individual or grouped destination control
- Individual or grouped transition control
- 64 user defined presets for one button recall of inputs, effects, and group settings
- Firmware synchronization throughout the system
- T-Bar for manual transition control
- Effect selection for single screen or multi-screen effects
- Direct control of each aux output or aux queuing for next transition
- Support for multiple setup files per input

视频输入

Universal A/V Inputs: (16) high bandwidth video channels  
 High-Resolution Video: Supports conversion of RGB videos with horizontal scan rates up to 100 KHz and resolutions up to 1600x1200. HDTV 480p, 720p, and 1080i formats are supported in RGB colorspace. Input levels are independently programmable.  
 Standard Video: Accepts RGB, Y Pb Pr, S-Video (Y/C), or NTSC/PAL video formats. Input levels are independently programmable for RGB and Y Pb Pr sources. Programmable luminance and chrominance levels are provided for S-Video, and Hue and Saturation controls are provided for NTSC/PAL inputs.  
 Synchronization: The unit automatically locks to the incoming video source.  
 Input Sync Signals: Sync-on-Video; Separate C or H/V  
 Connectors: BNC

视频输出

High-Resolution RGB Video: User programmable output formats; VGA (640x480), SVGA (800x600), XGA (1024x768), SXGA (1280x1024), For plasma displays, 832x624, 848x480, 852x480, 1280x768, 1365x768, 1365x1024. Also provides HDTV 480p and 720p output rates.  
 Main Outputs: Two independently buffered channels: (1) RGBHV with five BNC connectors; (1) RGBHV with HD-15 connector.  
 Preview Output: (1) RGBHV with HD-15 connector  
 Output Sync Type: Separate C or H/V

混合和过渡效果

13 transition effects including: cuts, fades, dissolves, curtains, grids, and wipes with variable transition rates  
 Picture-in-Picture: Supports display of two independently scaled windows.  
 Luminance Keying: Supports image overlay features with user-adjustable luminance key levels

物理的

Height: 17.50" (44.5 cm)  
 Width: 17" (43.2 cm) or 19" (48.3 cm) with rackmount option  
 Depth: 20.25" (51.4 cm)  
 Weight: 45 lbs (20 kg)  
 Shipping Weight: 52 lbs (23 kg).

输入电源

85-250 VAC, 50-60 Hz, 250 W maximum

环境

Temperature: 0-40 degrees C; Humidity: 0-95% noncondensing.

保修期

All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.

生成于: 16 Mar 2023

技术规格随时变化, 不会事先通知。请访问[www.barco.com.cn](http://www.barco.com.cn), 获取更新信息。