

OverView DR120

DLP™ based projector with SXGA resolution for retro enclosure.



일반 사양	
해상도	SXGA
DMD 칩	1280x1024 pixels
화면 비율	4:3 / 5:4
램프	120W UHP lamp
AC 전원	100-240 VAC, 2.5-1.0 A, 50-60Hz
전원	230 Watts
열 소산	< 750 BTU/h
밝기	800 ANSI Lumen
명암비	1000:1 (full white/full black)
컬러	Dynacolor™ allows the user to digitally set primary and secondary color coordinates Linked Dynacolor™ automatically adjust multi-channel display walls to a common color triangle
입력	• 1 x input for RGB/RGSB/RGBS/RGBHV (5 x BNC) • 1 x VGA (D-15 connector)
크기 구조	• Width 535 mm / 21.1 in. • Height 296 mm / 11.7 in. • Depth with lens 354 mm / 13.9 in. • Depth 278 mm / 10.9 in. • Weight 20kg / 44.1lbs • Shipping weight (max.) 35kg / 77.2 lbs

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.

