

D- Cine Premiere Console Kinot



技术规格**D-CINE PREMIERE CONSOLE KINOTON EUR****一般规格**

综合	Kinoton, SK25DC console.
灯泡	Optional 2kW, 3kW, 5kW, and 7kW Xenon Arc lamp depending on screen size.
反射镜	Standard f2.0 dichroic glass type
电源	-Lamp power supply -EUR version -IREM 3-7 kW three phase 360-460V 50 Hz -Lamp Power supply -USA version -IREM 3-7kW three phase 187-230V 60 Hz

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。