

ELM G10



技術仕様

ELM G10

一般仕様	
光出力	10,000 ANSI lumen
DMDデバイス	3 high resolution XGA DMD's
解像度	1024 x 768 (native) 1280 x 1024 (max)
輝度均一性	> 90% for the total screen area
コントラスト	Normal mode: 450 : 1 High mode: N/A (Full White / Full Black)
ランプ	Lifetime (max): 1000 Hrs Lifetime (typ): 750 Hrs
主要電源	Lamp Power: 3.0 kW 185V -260V
互換性	• All current Video sources in Composite, S-VHS, RGB or Component or Serial Digital format • All currently proposed HDTV, extended and improved television standards (1080i, 720p,...) • Computers and workstations with a resolution of up to 1280 x 1024 • Most Macintosh computers • Two digital input slots to allow for direct digital interfacing with current and future digital standards
消費電力	3.750 Watt
周囲温度	40°C (104°F) max
寸法	1.465 mm x 760 mm x 554 mm 57,7" x 29,9" x 21,8"
重量	135 kg / 298 lbs
レンズ	QLD zoom lenses have been designed for high resolution SXGA projectors. The throw is 25% longer when used with XGA DMD panels.
シームレスな切り替え	Not available
ScenergiX	Not available
レンズシフト	QLD Lenses Motorized V shift: up to 175% Motorized H shift: up to 160% LD Lenses Motorized V shift: up to 105% Motorized H shift: up to 70%
シールドエンジン	No
ネットワーク接続	Not available
固定入力	• 1 Multifunctional 5-cable input for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals • 1 RGB analogue input with standard sync (BNC connectors), sync on green or separate sync
オプション入力	• 1 SDI input (Serial Digital Input) Two free analog input slots for optional input modules: • Video/S-Video Input: Video on BNC, S-Video on 4-pin mini-DIN connector • Component Video Input (Y, R-Y, B-Y, S) on 4 BNC connectors • RGB analogue input with tri-level sync (BNC connectors), sync on green or separate sync One free digital input slot for optional digital input modules: • SDI • HD -SDI
リモート・コントロール	• RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

