

# DP4K-17BLP

Smart Laser cinema projector for screens between 13-18m (43-59 ft)



- **Reduced total cost of ownership**
- **Unprecedented ease of mind**
- **Superior image quality**

The DP4K-17BLP delivers consistent, razor-sharp, and high-contrast images with native 4K resolution and 17,000 lumens brightness. It's perfectly suited for mid-size movie screens ranging from 13 up to 18 meters (43 up to 59 feet).

#### **Reduced total cost of ownership**

Eliminating all lamp-related costs, the DP4K-17BLP provides a very attractive TCO. Thanks to its unique cooling system, the projector boasts a 30,000-hour constant brightness at typical usage conditions. Its significantly higher optical efficiency results in electricity bill savings of up to 40%.

#### **Unprecedented ease of mind**

The DP4K-17BLP cuts operating expenses, reduces operational complexity, and optimizes labor cost. The projector increases your uptime and frees you from all lamp-related costs, administration, and maintenance.

#### **Superior image quality**

The DP4K-17BLP offers consistent DCI-compliant image quality with native 4K resolution, outstanding uniformity, and higher contrast on white and silver screens. Its light output can be dimmed to 30% of the initial brightness, enabling 2D and 3D showings from the same projector.

#### **Retrofit ready**

If you already own a Barco B-series projector you can replace your current lamp house with the unique laser phosphor retrofit module through an easy on-site upgrade.

**Product specificaties****DP4K-17BLP**

| General specifications                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Helderheid                                     | 17,000 lumens (typical)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Native contrastverhouding                      | 2,000:1 (typical)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Primelenzen                                    | 1.13-1.72; 1.35-1.86; 1.46-2.10; 1.65-2.60; 1.95-3.26; 2.53-4.98                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Resolutie                                      | 4,096 x 2,160                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Langdurige stabiliteit van helderheid          | 30,000 hrs @ average usage conditions                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Afmetingen (B x L x H)                         | Projector: 754 x 1,129 x 604 mm / 29.69 x 44.5 x 23.78 inches<br>Cooler: 561.5 x 738.5 x 348 mm / 22.11 x 29.07 x 13.7 inches                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Gewicht                                        | Projector: 144kg (318 lb)<br>Cooler: 32kg (70.6 lb)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Lengte koelvloeistofslang                      | 4 hoses; 0.5m, 2.5m, 5m, and 8m (1.6ft/8.2ft/16.4ft/26.2 ft)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Verticale scheiding tussen koeler en projector | Maximum 3m (10ft) (higher or lower)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Voedingsvereisten                              | Projector: single phase 200-240V 15A<br>Cooler: obtains power from the projector                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Warmtebelasting (max. vermogen)                | 7526 BTU/h                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Omgevingstemperatuur                           | 35°C (95°F) Max. (projector and cooler)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Omgevingsvochtigheid                           | 85% Max. (projector and cooler)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Energieverbruik                                | Projector (incl. cooler): 2.4 kW                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Mediaserver                                    | BarcoAlchemy ICMP and other IMB brands supported.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Geluidsniveau                                  | dB(A) @ 1 m:<br>67.6 dB(A)<br>62 dB(A) (half fan speed)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| 3D-systemen                                    | Active glasses systems and polarization systems on silver screens are supported. Color separation systems (Dolby3D and 6P) are not supported.                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Veiligheidsvereisten                           | Class 1 risk group 3 Show safety: the customer shall take precaution for the laser safety (respect the hazard distance and separation height) according to local laser show safety regulations. Workplace safety: the customer shall take precaution for: <ul style="list-style-type: none"><li>■ workplace safety as prescribed by the local authorities</li><li>■ basic laser safety training for operators</li><li>■ laser safety program implementation in the company;</li><li>■ access limitation only to trained personnel: area labelling, etc.</li></ul> |

**Laatst bijgewerkt: 17 May 2023**

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.