

wePresent SharePod

With the push of a button, connect any HDMI compatible device into a wePresent environment



- **Wireless mirroring for HDMI sources without software or configuration required**
- **Easy guest, one-touch connection for guests in any wePresent environment**
- **Utilize on board interactive and collaboration features such as annotation, WebSlides and more with devices connected via SharePod**

Coupling SharePod and wePresent

SharePod allows any HDMI source to utilize the advanced features on the wePresent device such as the 4-to-1 projection, onscreen annotation, WebSlides and more. SharePod pairs to any wePresent wireless presentation system. Connect your HDMI source to the SharePod, press the button and begin presenting your HDMI device.

Expanding possibilities in technology driven learning environments

SharePod improves learning experiences by bringing more devices into the learning environment. Utilize document cameras, HDMI microscopes or other instruction tools by connecting them to your wireless presentation environment via SharePod.

Safe connections for security sensitive environments and guests

In financial, government and other environments, security of the network and individual devices is a high priority. SharePod provides secure, controlled guest access to wePresent's interactive and collaborative presentation features without compromising network security. Simply connect SharePod via an HDMI cable, press the button and begin presenting. SharePod is an easy connection method for any guest that takes little time and effort and only requires an HDMI out port from their device.

Expand your presentation options while keeping your network secure using SharePod.

Product specificaties**WEPRESENT SHAREPOD**

General specifications	
Standaarden	IEEE 802.11a/b/g/n 5G/2.4GHz IEEE 802.3(10BASE-T)/IEEE 802.3u(100BASE-TX)
Gegevenssnelheid draadloos	up to 300Mbps
Protocol	MirrorOp TCP/IP
IP-configuratie	automatic: DHCP client manual: Static IP address
Beheer	USB auto pairing web-based configuration
HDMI	supports HDMI V1.4 (Does not support DHCP content)
Beveiliging	IEEE Standard 64/128 bit WEP WPA WPA2-PSK
Transmissievermogen	2dBi
Gevoeligheid ontvanger	802.11b: 11M -76 dBm 802.11g: 54M -67dBm 802.11n: 65M HT20 -64dBm 150M HT40 -61dBm
Antennes	internal PIFA antenna
Bereik	up to 100m
Video-uitgang	1280x720 (720P) 1920x1080 (1080i/1080p)
Vermogen	External Power adaptor 5V DC input 1.2A
Interfaces	1 x HDMI (front) 1 x Micro USB (back) 1 x RJ-45 Ethernet LAN (back)>br /> Reset Button (back)
Led-beeldscherm	connection status, playing status
Afmetingen	109 x 106 x 33mm (without packaging)
Gewicht	187g (without packaging)
Bereik bedrijfstemperatuur	0~40°C
Operationele vochtigheid	80%
Bereik opslagtemperatuur	-10°C~60°C
Vochtigheid bij opslag	90%
Certificeringen	FCC/CE
Garantie	24 months

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.