

TruePix TP1.5-E

屋内向けの用途に適した、1.5mmピクセルピッチの高解像度LEDディスプレイ



- スマートエンジニアリングによって真にシームレスな映像を保証
- 24時間365日、スムーズで効率の良い作動を保証
- あらゆる照明環境下で、優れた色再現度を実現
- 環境負荷を低減
- 最長5年間の専用サービスとサポート

TruePix TP1.5-Eは、Barcoの新しい主力屋内高解像度LEDプラットフォームです。27.5インチのタイルはアスペクト比16:9で、ピクセルピッチはわずか1.5mmです。TruePixは、コントロールルーム、企業、ブロードキャストなどのビジュアライゼーション用途向けに設計されており、周囲光や制御照明に晒される環境にも対応できます。

真にシームレスな映像を実現

TruePixは、数十年間の経験に基づいて、LEDビデオウォールが提供する体験を新たな水準へと引き上げています。このソリューションは、スマートエンジニアリングと次世代のInfinipix®であるInfinipix® Gen2を組み合わせることで、意図したとおりにコンテンツを実現し、予測可能で真にシームレスな映像の実現を保証します。24時間365日、スムーズで効率の良い作動が保証されるため、いつでも安心してご使用いただけます。

Barco TruePixのスマートエンジニアリングは、リスクのない正確な設置によって視覚的な歪みを取り除く、独自のメカニカルコンセプトを取り入れています。TruePixの卓越したシームレス性と平面性は、ガイド付きモジュール配置と自動水平調整マウントによって実現されています。Barco独自の画像処理システムであるInfinipix®の次世代製品、Infinipix® Gen2は、あらゆる輝度設定レベルにおいても優れた色再現度を保証します。また、目の疲れを軽減しながら、コンテンツのニーズを柔軟かつ自動的にサポートします。

いつでも安心

途切れることのないデータフローによって、スムーズで効率の良い作動を24時間365日保証します。EcoPowerスタンバイモードで使用すれば、二酸化炭素の排出量を削減することができます。最大5年間の専用サービスとサポート(一貫した視聴体験の保証)により、製品の寿命全体にわたって安心してご利用いただけます。

技術仕様
TRUEPIX TP1.5-E

LED tiles	
Pixel pitch	1.588
Pixel per module	384x216 (HxV)
Aspect ratio	16:9
LED lifetime	100,000h (video -50% brightness)
Brightness	>600 nit
Peak brightness	780 nit
Internal processing	23 bit
Color depth	16 bit (281 trillion colors)
Shaders	Yes
Control	Infinpix® Gen2
Refresh rate @60Hz	3,840 Hz
3D	3D supported
Frame rate	24 -240 Hz
Hor. viewing angle	160° +/-5°
Vert. viewing angle	160° +/-5°
Brightness uniformity	>98%
Dimming	0-100%
Contrast	>7,000:1
Power consumption	703 W/m ² 147 W/Tile (max) 197 W/m ² 41 W/Tile(typ)
Heat dissipation	2,394 BTU/h/m ² (max) 672 BTU/h/m ² (typ)
Ceiling configurations supported?	Yes
Heat dissipation front/back	54%/46%
Operation power voltage	AC power: 100-240V 50/60Hz DC power: Input: 36-55Vdc 16A (max.) Output: 36-55Vdc 10.72A/36V (max.) or 12.55A/55V (max.)
Operational humidity	10 -80%
Operational temperature	-10°C to +40°C / 14°F to 104°F
Storage temperature	-20°C to +60°C / -4°F to 140° F
Storage humidity	15 -85%
Redundancy	Power: Optional Standard on REM tiles Data: Standard Inter-tile redundancy Embedded signal loop redundancy Optional N + N redundancy
HDR	HLG / HDR10 supported

技術仕様**TRUEPIX TP1.5-E**

Concave curvature	Up to 10° standard curved tile (3.5m radius) Up to 5° curved modular tile (3.5m radius)
Convex curvature	Up to 3° standard curved tile (12m radius)
Ceiling configurations supported?	Yes
Dimensions	(WxHxD) 609.92x343.08x71mm / 24.01"x13.5"x2.80"
Weight	Standard / curved tiles: 8.3kg/tile (single PSU) / 8.7kg/tile (dual PSU) Modular curved tiles: 9.1kg/tile (single PSU) 9.5kg/tile (dual PSU)
Serviceability	Full front & full back service Modular curved tile -Full front & full back service (PSU only back access)
Cable management	No external cabling
Installation	Self-leveling with surface tolerance compensation
Module replacement	Automated parallel motorized extraction
Module placement	Guided module placement
Ergonomics	SteadyView™ driver algorithm to reduce eye fatigue
Certifications	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
TAA Compliancy	Not available
Warranty	3 years
EssentialCare Service offering	5 years with LED batch compatible modules

生成日:09 May 2024

技術仕様は予告なく変更する場合があります。最新情報については、www.barco.com をご覧ください。