

# SLM R8 Performer

A Compact Projector for Rental & Staging Applications



## Specifiche tecniche

## SLM R8 PERFORMER

Specifiche generali	
Emissione luminosa	8.000 ANSI Lumen
Digital MicroMirror Device™	3 high resolution SXGA DMD™s
Risoluzione	1280 x 1024 (SXGA)
Uniformità della luminosità	> 90 % for the total screen area
Contrasto	Normal mode: 800:1 High mode: 1600:1 (Full White/Full Black)
Lampada	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs  Lamp Power: 2,0 kW
Livello di rumore (a 20° C)	
Livello di rumore (a 40° C)	
Tensione di alimentazione	200 -240 V
Consumo energetico	2.550 W
Temperatura ambiente	35°C (95F) max
Dimensioni	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Peso (compresi elementi di assemblaggio)	57 kg (126 lbs)
Ottiche	BARCO's "click-and-play!" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Spostamento obiettivo	Motorized V shift: up to 100% Motorized H shift: up to 65%
Elemento centrale DLP™ sigillato	No
Commutazione continua	Standard
ScenergiX	Standard
Connessione in rete	Optional
Ingressi fissi	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals  · 2 Multistandard DVI  · SDI input (Serial Digital Input)
Ingressi opzionali	One free digital input slot for optional input modules:  · SDI  · HD -SDI
Comando da remoto	• RS232 or RS422 loop-through input (D9-connector) for PC based projector control  • Communication input (D9-connector) for peripherals  • 3 pin male XLR connector for wired remote (standard remote)  • 3 pin female XLR connector for bi-directional communication (rugged remote)

Generato il: 15 Mar 2023

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.<br /> L'ultima versione di questo opuscolo è disponibile all'indirizzo [www.barco.com](http://www.barco.com).