

H 2.0 Quad input card



- Four HDMI™ 2.0 connectors
- Supports up to 4x 1600p60, or 2x 4K@60p/UHD per card (single cable)

Supports up to 4x 1600p60, or 2x 4K@60p/UHD per card (single cable)

- HDCP 2.2 compliant

HDCP 2.2 compliant

- EDID support for VESA/CEA, and custom timings

EDID support for VESA/CEA, and custom timings

- Automatic input acquisition and configuration

Automatic input acquisition and configuration

Product specifications**H 2.0 QUAD INPUT CARD****General specifications**

| | |
|-----------------|---|
| Connectors | 4x full sized HDMI™ connectors |
| Resolution | up to 2x 4096x2160@60p in (8L) slot |
| Color depth | 8-bit; 10-bit; 12-bit (DL or lower) |
| Color sampling | up to UHD@60p 8-bit 4:4:4 or 10-bit 4:2:2 |
| HDCP | HDCP 2.2 compliant |
| Signal capacity | 600 MHz |

Specifications when used with Encore3

| | |
|------------------|---|
| Connectors* | 4x full sized HDMI™ 2.0 connectors |
| Resolution* | Support up to 4x 4096x2160 @60Hz |
| Color depth* | 8-bit; 10-bit; 12-bit |
| Color sampling* | up to UHD@60p 8-bit 4:4:4 or 10-bit 4:2:2 |
| HDCP* | HDCP 2.2 compliant |
| Signal capacity* | up to 4096x2160 @60Hz |

* Specification when used with Encore3

Last updated: 30 Jan 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.