

SLM G10 Performer

A compact and Powerful Projector for Rental & Staging Applications.



Product specificaties**SLM G10 PERFORMER**

General specifications	
Lichtuitvoer	10.000 ANSI Lumen
Resolutie	1024 x 768 (native) 1600 x 1200 (max)
Resolutie	1024 x 768 (native) 1600 x 1200 (max)
Digital MicroMirror Device™	3 high resolution XGA DMD™'s
Helderheidsuniformiteit	90 %
Contrast	Normal mode: 500 : 1 High mode: 1000 : 1 (Full White/Full Black)
Lamp	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs Lamp power: 2,2 kW
Geluidsniveau (bij 20°C -68°F)	< 56
Geluidsniveau (bij 40°C -104°F)	< 58
Netspanning	200-240 V
Energieverbruik	2750 W
Omgevingstemperatuur	35°C (95F)
Grootte	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Gewicht (inclusief takeluitrusting)	57 kg (126 lbs)
Lenzen	BARCO's "click-and-play"™ TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lensverschuiving	Motorized V shift: up to 118% Motorized H shift: up to 65%
Verzegelde DLPT™-kern	No
Naadloos schakelen	Standard
ScenergiX	Standard
Netwerkverbinding	Optional
Vaste ingangen	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input)
Optionele ingangen	One free digital input slot for optional input modules: · SDI · HD -SDI
Afstandsbediening	• RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.