

# G62-W14

13,600 lumens, WUXGA, DLP laser phosphor projector



- **Great image quality**
- **Optimal integration capabilities**
- **4K compatible and 3D-ready**
- **Guaranteed service and support**

The G62-W14 expand the single-chip offering with a quality WUXGA projector of 13,600 lumens. It opens up the possibilities to a wider range of applications while still relying on the valued Barco service and support.

The laser phosphor light source ensures great image quality on the one hand, but also lower maintenance compared to most lamp-based projectors on the market. Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer.

The G62 models enable HDMI 2.0 input capabilities and higher bandwidth than its predecessors, which makes them 4K compatible and 3D capable to visualize your high-quality content at its best.

The projectors are available in black and fully white chassis, allowing you to choose the perfect fit for your specific environment. Their uniform compact size, the compatibility with other Barco products and the wide lens shift range enlarge the projectors flexibility.

**Product specifications****G62-W14****General specifications**

Projector type	Single chip DLP laser phosphor projector
Resolution	1,920 x 1,200 (WUXGA)
Brightness	11,500 ANSI lumens 12,800 center lumens 13,600 ISO lumens
Brightness uniformity	90%
Contrast ratio	1,200:1 sequential; 6,000:1 dynamic; Extreme black: 750,000:1
Light source	Laser phosphor
Light source lifetime	Up to 20,000hrs
Aspect ratio	16:10
Orientation	360° rotation, no restrictions
Sealed DLP™ core	Yes
Color correction	Yes
CLO (constant light output)	Yes
Image processing	Embedded warp & blend possible via Ptoolset
3D	Active stereoscopic 3D
Lens type	G-lenses -0.36:1 / 0.37-0.4:1 / 0.65-0.75:1 / 0.75-0.95:1 / 0.95-1.22:1 / 1.22-1.53:1 / 1.52-2.92:1 / 2.90-5.50:1
Optical lens shift	Vertical up to 100%, depending on lens Horizontal up to 30%, depending on lens Motorized zoom and focus Motorized lens shift
Inputs	2x HDMI In (version 2.0) (with locking screw) / 1x DVI-D (only support digital signal) / 1x HDBaseT / 1x 3D SYNC In / 1x 3G-SDI
Input resolutions	Up to 4K @60Hz Refresh rates: 24Hz to 60Hz for WUXGA and 4K/4KUHD (4096 x 2160 / 3840 x 2160) 4K input signals will be scaled to the projector's output resolution
Software tools	Projector Toolset and Insight Management Suite (IMS)
Control	IR, RS232, RJ45, 3.5mm phone jack for wired remote
Network connection	10/100 Ethernet, RJ45
Power requirements	100-240V / 50-60Hz
Power consumption	810W nominal, 970W maximum
Standby power	less than 0.5W
BTU per hour	2,747 BTU/h nominal; 2883 BTU/h maximum
Noise level (typical at 25°C/77°F)	35dB(A) -39dB(A) depending on the used mode
Operating temperature	0 ~ 40 °C (sea level)
Operating humidity	10 -85% RH, non-condensing
Storage temperature	-10 ~ 60 °C
Storage humidity	5 -90% RH, non-condensing
Dimensions (WxLxH)	without feet: 484 x 529 x 195 mm / 19.1 x 20.8 x 7.7 inch with feet: 484 x 529 x 206 mm / 19.1 x 20.8 x 8.1 inch
Weight	without lens: 22.7 kg / 50.1 lbs
Standard accessories	Power cord, wireless remote control
Certifications	CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI
Warranty	Limited 3 years parts and labor

**Last updated: 30 May 2024**

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.