

BarcoGraphics 6300



- High light output of 2,200 ANSI lumen
- Native panel resolution of 1,024 x 768 pixels
- Vibrant images with remarkable depth and clarity
- Perfect geometry
- Razor sharp in every corner
- Exceptional input compatibility
- Impressive array of input connections
- Easy picture alignment through BARCO's AutoImage feature
- Direct stacking
- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement for older generation projectors

Especificaciones del producto**BARCOGRAPHICS 6300****Especificaciones generales**

Salida de luz	2200 ANSI Lumen
Paneles LCD	3 active matrix poly-silicon LCD panels (1.8" diagonal) with a resolution of 1,024 x 768 pixels (aspect ratio 4:3)
compatibilidad	All current Video sources in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280 x 1024 pixels/60 Hz Most sources with a pixel clock up to 135 MHz
contraste	>350:1 (full white/full black)
lámpara	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
tamaño de pantalla	For the zoom lenses : 1 -6 m For the 0.8 lens : 1 -1.7 m
peso	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 -25 kg / 46.3 -55.1 lbs.

Generado en: 09 Jul 2024

© 2024 Barco nv. Todos los derechos reservados. Prohibida la reproducción total o parcial sin autorización por escrito. Todos los nombres de marcas y de productos son marcas comerciales, marcas comerciales registradas o nombres comerciales de sus respectivos titulares. Debido a la innovación continua, la información y las especificaciones técnicas están sujetas a cambios sin previa notificación. Consulta www.barco.com para ver las especificaciones más recientes.