

# BARCOData 9200



**技術仕様****BARCODATA 9200****一般仕様****互換性**

Video sources in Composite, S-VHS, Component and RGB format  
Most computer signals from PC graphics boards : CGA, EGA, VGA, S-VGA, XGA, up to 1180 x 900 pixels/60 Hz  
Most Macintosh computers  
Electronic workstations with a resolution up to 1180 x 900 pixels/60 Hz  
Most computer sources with a pixel clock

**コントラスト**

>180:1 (on 5x4 B/W checkerboard)  
>340:1 (full white/full black)

**光出力**

6000 Lumen full white  
5000 ANSI Lumen

**対応スクリーンサイズ**

Min.: 1 m x 0.75 m (3.3' x 2.5')  
Max.: 15 m x 11.25 m ( 50' x 37.5')

**生成日:09 Jul 2024**

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。