

RLM H5 Performer

With its compact design and sealed optics, the RLM G5 Performer has proven itself to be an ideal all-round projector suitable to both the rental and staging markets.



기술 사양

RLM H5 PERFORMER

일반 사양	
광 출력	4500 ANSI Lumen
해상도	1280 x 720 (native)
명암비율	1000 : 1 (full field)
고명암비 모드	Available with special lenses
밝기 균일도	> 90%
램프	2 x 250 W mercury max. lifetime: 1500 hrs typ. lifetime: 1000 hrs min. lifetime: 750 hrs
소음도(@ 20°C -68°F)	42 dBa
소음도(@ 40°C -104°F)	46,5 dBa
주위 온도	Max 40°C (104°F)
전력 소비	700 W
기본 전압	92-240 V
무게	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)
크기(WxLxH)	705 x 707,8 x 316,5 mm
라이트 셔터	Standard
실드 DLP™ 코어	Standard
ScenergiX	Standard horizontal and vertical electronic edge blending
무이음경계선(Seamless) 전환	Standard (wipes, fades, ...)
PIP(Picture-in-picture)	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
디지털 줌	Standard
렌즈 인코더	On zoom and focus (with TLD lenses)
연결 CLO(Constant Light Output)	not available
입력 소스 호환	1600 x 1200 (max. input)
고정 입력	1x configurable 5 cable (BNC) 1x composite Video (BNC) 1x S-Video (4-pin DIN) 1x analogue RGB (D15 Connector) 1x SDI/HDSDI (+ loop-through) 1x DVI (Digital Visual Interface)
모듈형 입력	not available
컨트롤	· 1 x RS-232 / 422 IN · 1 x RS-232 / 422 OUT · 1 x XLR female (2 way) · build-in RF remote transceiver (optional)

기술 사양**RLM H5 PERFORMER****변경 범위**

Lens	Shift Range
RLD 0.8	up-down: 35<=>35 left-right: 15<=>15
Other RLD	up-down: 130<=>40 left-right: 50<=>50
TLD (HB) 0.8	up-down: 90<=>50 left-right: 40<=>40
Other TLD (HB)	up-down: 140<=>50 left-right: 50<=>50

투사율

Lens	Throw ratio
RLD 0.8	0.64
RLD 1.5 - 1.8	1.2 - 1.44
RLD 1.8 - 2.25	1.44 - 1.8
RLD 2.25 - 3.0	1.8 - 2.4
RLD 3.0 - 4.5	2.4 - 3.6
RLD 4.5 - 7.0	3.6 - 5.6
TLD (HB) 0.8	0.8
TLD (HB) 1.6 - 2.0	1.6 - 2.0
TLD (HB) 2.0 - 2.8	2.0 - 2.8
TLD (HB) 2.8 - 5.0	2.8 - 5.0
TLD (HB) 5.0 - 8.0	5.0 - 8.0

주문 정보

R9010300

작성일: 15 Mar 2023기술 사양은 예고 없이 변경될 수 있습니다. 최신 정보는 www.barco.com에서 확인하십시오.