

BarcoReality 6300



- Light output of 2,000 ANSI lumen
- Native S-XGA LCD-panels (1,280 x 1,024)
- Dynamic images with remarkable depth and clarity
- Razor sharp in every corner
- Unmatched source compatibility
- Impressive array of input connections
- Easy picture alignment
- Direct stacking
- Motorized zoom, focus and lens shift
- Precise projection from any angle and distance to the screen
- Easy replacement for older generation projectors
- Easy installation in front or rear screen configuration, in table or ceiling-mount

Product specificaties**BARCOREALITY 6300****General specifications**

Lichtuitvoer	2000 ANSI Lumen
Lcd-panelen	3 active matrix 1.8" diagonal S-XGA poly-silicon LCD panels (aspect ratio 5:4)
Compatibiliteit	All Current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV,...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic Workstations with a resolution up to 2000 x 1280 pixels / 76 Hz Most sources with a pixel clock up to 200 Mhz
Contrast	> 350:1 (full white/full black) > 120:1 (5x4 Checkerboard)
Lamp	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
Schermaformaat	From 1-6 m, except for the QGD (0.8:1) lenses
Gewicht	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 -25 kg / 46.3 -55.1 lbs.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO