

BarcoData 8200



Product specifications**BARCODATA 8200****General specifications**

| | |
|--------------|--|
| Light output | 2,500 ANSI lumen |
| Resolution | VGA, SVGA, XGA up to 1180 X 900 pixels |
| Contrast | >350:1(full white/ full black) |

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.