


# TruePix TP1.5

1.5 mm pixel pitch, high-res indoor LED display



- **Smart engineering guarantees truly seamless outcomes**
- **Smooth and efficient operations, 24/7**
- **Superb color accuracy, under all lighting conditions**
- **Reduced ecological footprint**
- **Up to 10 years of dedicated service and support**

TruePix TP1.5 is Barco's new flagship indoor high-resolution LED platform. The 27.5" inch tiles, with a 16:9 aspect ratio, have a pixel pitch of only 1.5 mm. TruePix is designed for control room, corporate and broadcast visualization applications and supports both environments exposed to ambient light and controlled lighting environments.

### Truly seamless outcomes

TruePix sets a new standard for the LED video wall experience based on decades of experience. The solution brings content to life as intended and ensures predictable, truly seamless outcomes, by combining smart engineering and Infinipix™ Gen2, the next generation of Infinipix™. Smooth and efficient operations are guaranteed 24/7, next to full peace of mind.

Barco TruePix' smart engineering introduces a unique mechanical concept for risk-free and precise installations, eliminating visual distortion. This unmatched seamlessness and flatness are achieved through guided module placement and self-leveling mounts. The next generation of Barco's proprietary Infinipix™ processing – Infinipix™ Gen2 – guarantees full image integrity at any brightness level, together with superb color accuracy. It flexibly and automatically supports any content need while reducing eye fatigue.

### Peace of mind at any time

Smooth and efficient operations are guaranteed 24/7 through uninterrupted data flows. Users can reduce the carbon footprint by using the EcoPower standby mode. Up to 10 years of dedicated service and support (ensuring a uniform viewing experience) to allow for peace of mind during the entire product lifetime.

**Product specificaties****TRUEPIX TP1.5**

<b>LED-tegels</b>	
Pixelpitch	1.588
Pixels per module	384x216 (HxV)
Beeldverhouding	16:9
LED-levensduur	100,000h (video -80% brightness)
Helderheid	>800 nit
Piekhelderheid	1040 nit
Interne verwerking	23 bit
Kleurdiepte	16 bit (281 trillion colors)
Shaders	Yes
Controle	Infinipix™ Gen2
Vernieuwingssnelheid @60Hz	3,840 Hz
3D	3D supported
Framesnelheid	24 -240 Hz
Hor. kijkhoek	160° +/-5°
Vert. kijkhoek	160° +/-5°
Uniformiteit van de helderheid	>98%
Dimmen	0-100%
Contrast	>9,000:1
Energieverbruik	734 W/m <sup>2</sup> 154 W/Tile (max) 217 W/m <sup>2</sup> 45 W/Tile (typ)
Warmteafvoer	2501 BTU/h/m <sup>2</sup> (max) 730 BTU/h/m <sup>2</sup> (typ)
Plafondconfiguraties ondersteund?	Yes
Warmteafvoer voor/achter	54%/46%
Bedrijfsspanning	AC power: 100-240V 50/60Hz DC power: Input: 36-55Vdc 16A (max.) Output: 36-55Vdc 10.72A/36V (max.) or 12.55A/55V (max.)
Operationele vochtigheid	10 -80%
Operationele temperatuur	-10°C to +40°C / 14°F to 104°F
Opslagtemperatuur	-20°C to +60°C / -4°F to 140°F
Vochtigheid bij opslag	10 -80%
Redundantie	Power: Optional Standard on REM tiles Data: Standard Inter-tile redundancy Embedded signal loop redundancy Optional N + N redundancy
HDR	HLG / HDR10 supported
Concave kromming	Up to 10° standard curved tile (3.5m radius) Up to 5° curved modular tile (3.5m radius)
Convexe kromming	Up to 3° standard curved tile (12m radius)
Plafondconfiguraties ondersteund?	Yes
Dimensies	(WxHxD) 609.92x343.08x94mm / 24.01"x13.5"x3.70"
Gewicht	Standard / curved tiles: 8.3kg/tile (single PSU) / 8.7kg/tile (dual PSU) Modular curved tiles: 9.1kg/tile (single PSU) 9.5kg/tile (dual PSU)
Onderhoudsgemak	Full front & full back service Modular curved tile -Full front & full back service (PSU only back access)
Kabelbeheer	No external cabling
Installatie	Self-leveling with surface tolerance compensation
Vervangen Module	Automated parallel motorized extraction
Plaatsen Module	Guided module placement
Ergonomie	SteadyView™ driver algorithm to reduce eye fatigue
Certificeringen	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
TAA-conformiteit	Optional
Garantie	3 years
EssentialCare-serviceaanbod	10 years with LED batch compatible modules

**Laatst bijgewerkt: 13 May 2025**

© 2025 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.