

iQ R210L



Specifiche tecniche

IQ R210L

Specifiche generali

Emissione luminosa	2,200 ANSI lumen
Uniformità della luminosità	Brightness uniformity: >95 % for the total screen
Pannelli LCD	3 active matrix 1.4" diagonal SXGA+ polysilicon LCD panels with Micro Lens Arrays and a resolution of 1400 x 1050 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Risoluzione	1400 x 1050 (native)
Lampada	2x 120 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.
Obiettivi disponibili	- Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (Long throw). - Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.
Larghezza schermo consigliata	From 1-6m / 3-20ft.
Rapporto di contrasto	> 800:1 (full white/full black)
Frequenze di scansione	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Caratteristiche speciali	- Standard cable basket - Standard light shutter - Advanced digital zoom - Advanced picture-in-picture - Seamless switching with effects
Compatibilità	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, s-VHS, component -All currently proposed HDTV extended and improved television standards (1080i, 720p...) -All computer graphics formats from VGA, S-VGA, XGA, S-XGA to U-XGA -Most Macintosh computers -Electronic Workstations with a resolution of up to 1600x1200 at 75Hz -Most sources with a pixel clock up to 160MHz -DVI sources up to SXGA+
Ingressi	• 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. • 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) • 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) • 1x VGA (D15 connector) • 1x DVI (Digital Visual Interface)
Comunicazione	• 1x D9 connectors for RS232 In/Out • 1x spherical IR receiver
Livello di rumore	
Alimentazione CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Consumo energetico	Max 350 Watt
Dissipazione alimentazione	
Norme di sicurezza	Compliant with UL1950 and EN60950
Interferenza elettromagnetica	Barco's iQ Series complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
Peso	Net weight: Body only 12.9 kg/ 28.5 lbs Shipping weight: without lens max. 17.5 kg / 38.5 lbs with lens max. 20 kg / 44 lbs

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.