


RetroData 808s



Product specifications**RETRODATA 808S****General specifications**

Light output	Economy mode: 139 Nit/41 ftl Normal mode: 195 Nit/57 ftl Boost mode: 214 Nit/62 ftl
Resolution	10 lp/mm at 50% MTF throughout the field
Contrast	SXGA 1280 x 1024

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.