


LD150-8

Barco's LD LED display solution wraps all the desirable LED qualities of brightness, dependability, long lifetime and low maintenance into an affordable package that meets all your requirements for dynamic digital



Especificaciones del producto	
LD150-8	
Especificaciones generales	
Tamaño de la pantalla	diagonal: 152" W x H: 3136mm x 2240 mm (124" x 88") surface: 7 m² (76 ft²)
Tipo de LED	3-in-1 SMD
Profundidad de pixel	8 mm
resolución	392 x 280
brillo	1200 NIT 1000 NIT (display calibrated at 6500° K)
angulo de visión horizontal	145° + (min 50% brightness)
angulo de visión vertical	145° + (min 50% brightness)
tiempo de vida	100.000h (typ. use) 45.000h (full white -half brightness)
procesado	+12 bit/color
colores	68.7 billion
tasa de refresco	400 Hz
consumo de potencia	2.800W (Avg) 11.200W (Max)
rango de temperatura	operating: 0° to 40°C (32° to 140°F) storage: -20° to 60°C (-4° to 140°F)
Dimensiones de cabina	width: 3372mm (133") height: 2476mm (98") depth: 330mm (13")
peso	760kg -1675lbs (excl. opt. mounting)
Dispositivo de procesamiento de imágenes	D2