


TF20

20mm pixel pitch, 6,000 nits outdoor LED tile for fixed installation



Featuring contrast-enhancing shaders

The TF20 features environmentally friendly technologies that reduce light pollution, such as contrast-enhancing shaders that allow for lower brightness and lower power consumption as well as a higher visual performance and a downward angle on its LEDs. This ensures that light is well targeted at your audience and that less excess light is spilled, which leads to a lower power consumption and longer lifetime.

Product specifications**TF20****General specifications**

Pixel pitch	20.0 mm
Brightness	6,000 nits
LED configuration	1R, 1G, 1B tilted downwards
Pixel density	7,513/sqm 699/sqft 2,304/tile (48x48)
Hor. viewing angle	+70°/-70°
Vert. viewing angle	-30°/+15°
Power consumption	139W/m ² (average) 500W/m ² (max.)
Heat dissipation	474BTU/hr/m ² (typical)
Tile dimensions	Width: 960mm Height: 960mm Depth: 230mm
Weight / Tile	38 kg (83.77 lbs)
IP rating	IP65/54
Processing	16 bit/color
Serviceability	Front or back
Operating temperature	-20 to +50°C (-4° to 122°F)
Operational humidity	10-99%
Certifications	ETL, CE, FCC Class A, RoHS

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.