

# G50-W8

8,000 lumens, WUXGA, DLP laser phosphor projector



- **Smallest and lightest projector in its category**
- **Industry leading energy efficiency in the 5-8K lumens segment**
- **Consistent image quality over time**
- **Full range of interchangeable lenses (with widest lens shift)**
- **Guaranteed service and support**

The G50-W8 is an affordable and compact, yet powerful, single-chip WUXGA projector designed for single and multi-channel projections for boardrooms, museums, exhibitions, experience centers, and entry-level simulation applications. It is part of the economical G50 series and the Barco smart line projectors. With a great price-performance ratio, the G50s are the most compact and energy efficient projectors on the market.

The laser phosphor light source ensures great image quality, with superb colors and image uniformity. These are the smallest projectors in our offering with the highest light efficiency visualizing high-quality content at its best.

Their uniform compact size, the compatibility with Barco's extensive G-series lenses and the wide lens shift range enlarge the projectors flexibility, which allows you to choose the perfect fit for your specific environment.

In addition, G50 owners can benefit from the valued Barco service and support. The G50 allows for an Insights Management Suite subscription, our cloud-based IoT platform to monitor, diagnose and control your projectors. And thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer.

**Product specifications****G50-W8**

General specifications	
Projector type	Single chip DLP laser phosphor projector
Resolution	1,920 x 1,200 (WUXGA)
Brightness	7,500 ANSI lumens 8,300 center lumens 8,900 ISO lumens
Brightness uniformity	90%
Contrast ratio	1,200:1 sequential; 6,000:1 dynamic; Extreme black: 750,000:1
Light source	Laser phosphor
Light source lifetime	Up to 20,000hrs
Aspect ratio	16:10
Orientation	360° rotation, no restrictions
Sealed DLP™ core	Yes
Color correction	Yes
CLO (constant light output)	Yes
Keystone correction	Yes
Image processing	Embedded warp & blend possible via Ptoolset
3D	Active stereoscopic 3D
Lens type	G-lenses -0.37-0.4:1 / 0.65-0.75:1 / 0.75-0.95:1 / 0.95-1.22:1 / 1.22-1.53:1 / 1.52-2.92:1 / 2.90-5.50:1
Optical lens shift	Vertical up to 100%, depending on lens Horizontal up to 30%, depending on lens Motorized zoom and focus Motorized lens shift
Inputs	2x HDMI In (compliant with HDMI 2.0b, HDCP2.2) / 1 x Display Port (1.2a) / 1 x HDBaseT(HDCP1.4) / 1 x 3D SYNC In
Output	1 x HDMI Out (Loop through HDMI1/HDMI2/HDBaseT/DP) 1 x 3D SYNC Out 1 x DC 12V Out 1 x Audio out, 3.5mm phone jack
Input resolutions	Up to 4K @60Hz Refresh rates: 24Hz to 60Hz for WUXGA and 4K/4KUHD (4096 x 2160 / 3840 x 2160) 4K input signals will be scaled to the projector's output resolution
Software tools	Projector Toolset

**Product specifications****G50-W8**

Control	1 x RS232 (D-sub 9 pin) (PC Control) 1 x Wired In (3.5mm phone jack) (Remote In) 1 x RJ45 (LAN)
Network connection	10/100 Ethernet, RJ45
Speakers	10W / 6 Ohm *2
Power requirements	100-240V / 50-60Hz
Power consumption	500W @110V 490W @220V
Standby power	less than 0.5W
BTU per hour	1706 @110V 1672 @220V
Noise level (typical at 25°C/77°F)	34dB(A) -38dB(A) depending on the used mode
Operating temperature	0 ~ 40 °C (sea level)
Operating humidity	10 -85% RH, non-condensing
Storage temperature	-10 ~ 60 °C
Storage humidity	5 -90% RH, non-condensing
Dimensions (WxLxH)	without feet: 486 x 376 x 181.2 mm
Weight	without lens: 13 kg / 28.66 lbs
Standard accessories	Power cord, wireless remote control
Certifications	CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI
Warranty	Limited 3 years parts and labor
*Note	Brightness levels +/-10%

Last updated: 29 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.