

Eos

Scalable control unit for video walls



Product specifications

EOS

General specifications

General	<ul style="list-style-type: none">• PC ATX technology with Pentium® IV processor• up to 1GB main memory• Ethernet/FastEthernet• PC MF-II keyboard, PC compatible mouse• up to 20 m keyboard and mouse extension available
Operating conditions	0-40° C 30-105° F at max. 80% humidity (non condensing)
Power	95-230 VAC ± 10%, 60/50 Hz
Power consumption	300 W
Weight	approx 15.7 kg 34.6 lbs
Dimensions	<ul style="list-style-type: none">• 19" industrial case, height in rack unit: 4U• width case: 440 mm 17.32 in.• width with fixation: 482 mm 18.98 in.• depth case: 450 mm 17.72 in.• depth with handles: 502 mm 19.76 in.• height: 177 mm 6.97 in.• height with rubber feet: 183 mm 7.20 in.

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.