

D320 PL

Advanced image processing unit that allows you to control up to 4 sources on one LED or Projection display.



Product specificaties**D320 PL****General specifications**

Ingangen	4 optional inputs Front accessible Integrated video processing Auto sensing, hot swappable s-video, composite, YUV/RGB SDI, HD-SDI, DVI up to UXGA
Compatibiliteit	Barco LED Displays & projectors
Uitgang	DVI-A, DVI-D
Schaalbaarheid	Chaining for more inputs Stacking for more displays
Flexibiliteit	User defined inputs
Effecten	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Gewicht	+/-7 kg
Bedrijfstemperatuur	0°C <> 45°C
Vermogen	120W max auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Bestelgegevens	R9851550
Connectoren	RS 232 [RJ11]
Controle	through XLite toolset
Scaler	4 input channels [Data-Video] fully scalable to desired output resolution
Grootte	482mm x 53mm x 486mm
Grootte invoereenheden	103mm x 41mm x 181mm
Vensterpositionering	Intuitive positioning interface
Z-volgorde besturingselement	Instant modification of Z-order control, for each output window

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.