

SLM R9+ Performer

Compact, SXGA+ resolution and 9000 Ansi Lumen light-output.



기술 사양

SLM R9+ PERFORMER

일반 사양		
광 출력	9000 ANSI Lumens 9500 Center Lumens	
해상도	1400 x 1050 (native)	
밝기 균일도	> 90% for the total screen	
명암비율	1600 : 1 (full field)	
	High contrast mode: 2000 : 1	
디스플레이	3 Chip DLP SXGA+ (resolution of 1400 x 1050 pixels (aspect ratio 4:3)).	
기능	- Picture in picture - Seamless switching with effects - Standard light shutter - Rigging point - Carrying handle - High contrast mode - P7 color processin	
PIP(Picture-in-picture)	2 sources simultaneous	
입력	Fixed inputs 2x Configurable 5-Wire (BNC; incl. 2 video decoders) 2x DVI (Digital Visual Interface) Modular inputs Standard: 1x SDI (+ loop through) Optional: 1x HDSDI (+ loop through)	
출력	DVI out (1400 x 1050) of full screen composed image	
통신	1x RS-232C IN (D-9 connector) 1x RS-232C OUT (D-9 connector) 1x RS-232C IN (XLR connector) 1x 2way prop. protocol to Rugged remote (5 pins XLR connector) 1x prop. protocol (RJ45 connector) - mini-jack for wired remote control	
호환성	· All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats · All currently proposed HDTV, extended and improved television standards (1080i, 720p) · All computer graphics formats from VGA, SVGA, XGA, SXGA, full HD to UXGA · Most Macintosh computers · Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz · Most computer sources with a pixel clock up to 200 MHz · DVI sources up to SXGA+	
입력 소스 호환	max. input: up to 1920 x 1080 and 1600 x 1200	
스크린 크기	From 1-8m / 3-26ft recommended	
스캔 주파수	Pixel clock >162Mhz (UXGA 60hz)	
네트워크 연결	Optional (10 base-T)	
온보드 디스플레이 서버	Optional DIMM PC available Remote control projector over ethernet via webserver	
주위 온도	Max 35°C (95°F)	
램프	1.75 kW Xenon	
	Warranty univeral lamphouse: 1000 Hrs	
렌즈	Lens	Order nr
	TLD (HB) 0.8	R9842040
	TLD (HB) 1.2	R9840770
	TLD (HB) 1.6 - 2.0	R9842060
	TLD (HB) 2.0 - 2.8	R9842080
	TLD (HB) 2.8 - 5.0	R9842100
	TLD (HB) 5.0 - 8.0	R9842120
렌즈범위	Vertical: -10% to +110% Horizontal: -50% to +50% (small differences occur per lens type)	

기술 사양

SLM R9+ PERFORMER

렌즈 인코더	On zoom and focus (with TLD lenses)	
투사율	Lens	Throw ratio
	TLD (HB) 0.8	0.75
	TLD (HB) 1.2	1.1
	TLD (HB) 1.6 - 2.0	1.45 - 1.85
	TLD (HB) 2.0 - 2.8	1.85 - 2.55
	TLD (HB) 2.8 - 5.0	2.55 - 4.55
	TLD (HB) 5.0 - 8.0	4.55 - 7.3
	TLD+ (HB) 7.5 - 11.2	7.5 - 11.2
ScenergiX	Standard horizontal and vertical electronic edge blending	
실드 DLP™ 코어	Standard	
먼지 필터	Dense, high quality microfilters available as spare kit, in a 6-pack & 24-pack	
소음도	61 dBA (at 40°C)	
기본 전압	200-240 V	
전력 소비	2250 W	
소비 전력	Max 6830 BTU/h	
AC 전원	190V -255V (50Hz -60Hz)	
무게	56 kg (124 lbs)	
크기	WxLxH 585 x 876 x 429 mm (23.0 x 34.5 x 19.9 inch)	
안전 규정	Compliant with UL1950 and EN60950	
전자파 장애	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A	
주문 정보	Projector: R9010320 Spare lamp: R9841810 6-pack dust filters: R8454096K 24-pack dust filters: R84540924K	

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.

