

OverView fPR67-DL

67" Display Wall system integrating 3-panel Poly-Silicon LCD technology with SXGA resolution. Includes front access and dual lamp.



Specifiche tecniche

OVERVIEW FPR67-DL

Specifiche generali	
Risoluzione	SXGA
Proporzioni	5:4
Colori	16.7 millions
Lampada	• Dual lamp • 2 x 100 W • Operation time 2 x 8000 h (average) • 100% availability of display wall • Keeps track of the 2 lamp life times • Detects lamp failure • When switching from one lamp to the other, constant display quality is offered • 3 modes: Hot Stand-By: 2nd lamp is on so that the switching time in case of lamp failure of the master lamp is minimal Cold Stand-By: 2nd lamp is switched off during operation, will only be activated when a lamp failure is detected of the master lamp Auto Switch Mode: regularly switch every 500 hours
Alimentazione CA	100-240 VAC, 50-60 HZ
Alimentazione	• 330 W in hot standby • 220 W in cold standby
Luminanza	110 cd/m² 32 ftL
Luminosità	500 lumens
Contrasto	350:1
Uniformità della luminosità	>95 %
Struttura dimensioni	• Diagonal 67" • Width 1335 mm / 52.56 in. • Height 1068 mm / 42.05 in. • Footprint 690 mm / 27.17 in. • Depth 822 mm / 32.36 in. • Socket heigth (min) 606 mm / 23.86 in. • Socket heigth (max) 1288 mm / 50.71 in • Weight 133 kg / 239 lbs
Conformità ambientale	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F • Humidity 40%-60%, non condensing
Accesso anteriore	• To engine, both lamps & filters • No limitations to install the system against a back wall
Schermi	Black type screen with large viewing angles Download the brochure for more info on the principles and technologies

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.

