

BarcoGraphics 6400



- Native panel resolution of 1,024 x 768 pixels
- Vibrant images with remarkable depth and clarity
- Perfect geometry
- Razor sharp in every corner
- High light output of 3,000 ANSI lumen
- Exceptional input compatibility
- Easy picture alignment (AutoImage)
- Direct stacking
- Motorized zoom, focus and lens shift
- Easy lamp and lens replacement
- Easy installation in front or rear screen configuration
- Precise projection from any position or distance
- Easy replacement of older generation projectors

Product specificaties**BARCOGRAPHICS 6400****General specifications**

Lichtuitvoer	3000 ANSI lumen
Lcd-panels	3 active matrix 1.8" diagonal XGA polysilicon LCD panels with a resolution of 1024x768 pixels (4:3 aspect ratio). LCD panels are selected for a minimum of pixel defects.
Compatibiliteit	All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (1080i, 720p,...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280x1024 pixels/76 Hz Most sources with a pixel clock up to 135 MHz
Contrast	>300 : 1 (full white/full black) >150 : 1 (5 x 4 ANSI checkerboard)
Lamp	New 400 Watt metal-halide arc lamp pre-aligned for max. light output Typical lifetime: 1000 hours
Schermafmaat	From 1-6 m, except for the QGD (0.8:1) lenses
Gewicht	Body only: 17.7 kg/39.0 lbs. Body + lens: 21-25 kg/46.3-55.1 lbs.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.