

RetroGraphics 808s



- Single front surface-coated optical grade mirror
- 67" super fine pitch Fresnel/Lenticular-Blackstripe screen with very wide horizontal and vertical viewing angles
- High-definition 8" CRTs with electromagnetic focus system
- F1.1 color corrected hybrid liquid coupled lenses
- Optional built-in Video Line Doubler improves Video image quality
- Horizontal autolock scan frequency of 15-110 kHz
- RGB bandwidth of 120 MHz
- Vertical scan frequency of 37-200 Hz
- Displays all sources from VHS Video up to 1,600 x 1,200 pixel workstations

Product specificaties

RETROGRAPHICS 808S

General specifications

Compatibiliteit	Display compatibility of from VHS Video up to 1600 by 1200 pixel workstations Horizontal autolock scan frequency of 15-110 kHz Vertical scan frequency of 37-200 Hz RGB bandwidth of 120 MHz Universal connection possibilities
Contrast	>1000:1 (on full white / full black)
Lichtuitvoer	1250 Nit / 364 ftL. (at 10 % peak white) 139 Nit / 41 ftL ANSI (Economy mode) 195 Nit / 57 ftL. ANSI (Normal mode) 214 Nit / 62 ftL. ANSI (Boost mode)
Schermaformaat	(diagonal) 67" (1.7 m)

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

