

Versa® TILE T100

Creative LED light panel



Product specifications**VERSA® TILE T100****General specifications**

| | |
|---------------------|---|
| Pixel pitch | 100 mm (3.93 in) |
| Colors | Trillions (48 bit color per pixel) |
| Refresh rate | > 1000 Hz |
| Light output | 900 cd/m ² (nits) Calibrated |
| Viewing angle | 170 degrees (Lambertian) |
| Control | Versa DRIVE D3 |
| Power input | System: 100-240 VAC 50/60 Hz T100 Tile: 12 VDC from Versa COM |
| Power consumption | 32W/panel |
| Thermal dissipation | 58 BTU/h per panel |
| Pixels | 4 x 4 (16 tiles) |
| Dimensions | Length: 400 mm (15.75 in) Width: 400 mm (15.75 in) Depth: 51 mm (2.00 in) |
| Weight | 2 kg (4.41 lbs) @ 4 x 4 |

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.