

RetroGraphics 808s



- Single front surface-coated optical grade mirror
- 67" super fine pitch Fresnel/Lenticular-Blackstripe screen with very wide horizontal and vertical viewing angles
- High-definition 8" CRTs with electromagnetic focus system
- F1.1 color corrected hybrid liquid coupled lenses
- Optional built-in Video Line Doubler improves Video image quality
- Horizontal autolock scan frequency of 15-110 kHz
- RGB bandwidth of 120 MHz
- Vertical scan frequency of 37-200 Hz
- Displays all sources from VHS Video up to 1,600 x 1,200 pixel workstations

技术规格

RETROGRAPHICS 808S

一般规格

兼容性

Display compatibility of from VHS Video up to 1600 by 1200 pixel workstations
Horizontal autolock scan frequency of 15-110 kHz
Vertical scan frequency of 37-200 Hz
RGB bandwidth of 120 MHz
Universal connection possibilities

对比度

>1000:1 (on full white / full black)

光输出

1250 Nit / 364 ftL. (at 10 % peak white)
139 Nit / 41 ftL ANSI (Economy mode)
195 Nit / 57 ftL ANSI (Normal mode)
214 Nit / 62 ftL ANSI (Boost mode)

屏幕尺寸

(diagonal) 67" (1.7 m)

生成于: 08 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。