


E2 Tri-combo

Full sized 4K60p Event Master processor



- Full show control with pre-configured cards
- Native 4K60p input and output on a single cable
- Intuitive user interface

The Tri-combo configuration of the E2 features four Tri-combo input cards, and one Tri-combo output card. These new cards support 4K 60p on a single cable. With software version 6.0 and greater, the input cards support 2x 4K60p on a single cable or 6x HD inputs (when installed in dual capacity input slots). The Tri-combo output card supports 2x 4K 60p or 6x HD. This boosts the Tri-combo E2 configuration to an impressive 40 HD inputs or 12 4K60p inputs and up to 5 4K60p or 18 HD outputs. This new E2 has extra capacity and flexibility to support your growing shows.

Product specificaties

E2 TRI-COMBO

General specifications

| | |
|----------------------------|--|
| Model | NGS-4U |
| Live-effectcanvas | Up to 20 Megapixels PVW/PGM 40 Megapixels PGM only 80 Megapixels @30p and PGM only |
| Video-ingangen | <ul style="list-style-type: none">40 inputs via 8 input cards (HDMI/DP combo 4 inputs, Tri-combo 6 inputs per card)Up to 12x 4K inputs -(HDMI/DP combo 1x 4K@60p, Tri-Combo 2x 4K@60p per card)16x SDI SD/HD/3G/6G/12G connectors8 x HDMI 1.4a (297 MPix/sec max)4 x HDMI 2.0 (594 MPix/sec max)8 x DisplayPort 1.1 (300 MPix/sec max)4 x DisplayPort 1.2 (600 MPix/sec max) |
| Video-uitgangen | <ul style="list-style-type: none">18 HD outputs via 4 output cards (Event Master series cards)Up to 5x 4K outputsHDMI output card supports 1 4K60p or 4 HD. Tri-combo supports 2 4K60p or 6 HDTriCombo output card supports 4 x SD/HD/3G/6G/12G 1x HDMI 2.0, and 1x DisplayPort 1.2 connectors8x HDMI 1.4a (297 Mpix/sec max)3x HDMI 1.4a output cards support 4 HDMI connectors each. The top two connectors of the card support up to 297 MPix/sec (2560x1600 typical). The bottom two connectors support 165 MPix/sec (1920x1200 typical).The right most HDMI card (slot 14) may also be used as a two output Multi-viewer. |
| Genlock | Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD SSD Sync: 4x input Din connector, 2x output Din connector |
| Programma-uitvoer | <ul style="list-style-type: none">Up to 18 program outputs configurable as single screens or tiled/blended widescreens (preview and Multi-Viewer not available in all configurations)Up to 16x 2048x1200@60p or 4x 3840x2400@60pIndependent edge blending/feathering control for all four sidesTri-combo supports 90degree output rotation |
| Mixers | <ul style="list-style-type: none">Native resolution background mixer per output screenIndependent layer transitions or full Preview/Program transitionFlexible layer allocation – up to 16 mixable or 32 single scalable PIP/key layers assignable to Program output screens |
| Geheugenruimte voor foto's | Up to 100 HD or 25 UHD, depending on the import file size |
| Laageffecten | <ul style="list-style-type: none">Borders (hard, soft, halo) and drop shadowsColor effectsStrobe, H&V flipLuma, chroma and Cut/Fill keys (not all modes support keying)PIP moves via Keyframes |
| Multiviewer | <ul style="list-style-type: none">Flexible user-definable layoutsMonitor all Inputs and Outputs, including Preview and AuxTwo outputsDedicated hardware same as E2 Event Master Processor |
| Uitbreidbaarheid | <ul style="list-style-type: none">Easily expandable for larger display applications via proprietary linksLink units to increase available Inputs and Outputs for larger tiled/blended widescreen applicationsExpansion via simple linking<ul style="list-style-type: none">Up to 8 E2 chassis can be linked2 linking cables are included with each E2 chassis |
| HDCP | HDCP compliance determined by installed cards. |
| Onderhoudsgemak | <ul style="list-style-type: none">Field-Serviceable I/O and processing cards (not hot-swappable)Hot swappable dual-redundant power supplies |
| Geluidsniveau | Max 52.9 dB avg. Fans at 100%. Fan speed is software-managed based on operating temperature. Reference ISO 7779 |
| Afmetingen | Height: 17.8 cm (7.0 in) -4 RU Rack mount Width: 43.2 cm (17.0 in) -without chassis handles, 48.3 cm (19 in) with chassis handles attached Depth: 56.9 cm (22.4 in) from front panel to rear panel, 62.2 cm (24.5 in) overall |
| Gewicht | 31 kg (68 lbs) |
| Vermogen | <ul style="list-style-type: none">Input power: 100-240 VAC 50/60Hz 826 WattDual-redundant, hot-swappable power supplies |
| Garantie | 3 years parts and labor |
| Omgevingstemperatuur | 0-40° C (32-104° F) |
| Omgevingsvochtigheid | 0-95% Non-condensing |

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.