

DP-1500

2K Digital Cinema projector for screens up to 15m (49ft)



Product specificaties**DP-1500****General specifications**

Digital MicroMirror Device™	3 x 0.98" DC2K dark metal devices
Native resolutie	2048 x 1080
Behuizing	Hermetically sealed DMD™ and optical assembly
Schermbreedte	Screen width (screen gain 1.5) @ 14ftL * : 15m -50ft Screen width (screen gain 1.3) @ 14ftL * : 14m -45ft (*) = +/-10 variation possible between units
Montage	universal pedestal (optional)
Omgevingstemperatuur	max. 35°C / 95°F
Lamp	1.5kW -3kW Xenon lamp size Lamp power: 1.5kW -3kW
Contrastverhouding	2000:1
Digitale video-ingangen	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Primelenzen	Prime lens (1.2 - 1.8) 0.98" DC2K Prime lens (1.4 -2.05) 0.98" DC2K Prime lens (1.6 -2.5) 0.98" DC2K Prime lens (1.95 - 3.2) 0.98" DC2K Prime lens (2.4 - 3.9) 0.98" DC2K
Projectordiagnose	via PC touch panel via Communicator control software via SNMP agent
Voedingsvereisten	220V 14.000 BTU / hr (with 3kW lamp)
Afmetingen	Projector: 505(H) x 689(W) x 1018(D) mm 19.9(H) x 27.1(W) x 40.0(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	projector: 90kg (199lbs)
Opties	CLO-constant light output ACS-2048 SNMP agent motorized/memorized lens focus, zoom & shift automatic XYZ lamp alignment
Bestelgegevens	R9004443

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.