

BarcoReality 6400



- Extremely high light output of 3400 ANSI lumen
- Three active matrix 1.8" S-XGA Poly-Silicon LCD panels with Micro Lens Array (MLA) and a resolution of 1280 x 1024 pixels
- BARCO's advanced True Color Reproduction feature processes conventional video signals and transforms them into brilliant images with vibrant colors and amazing color depth
- BARCO's patented Pixel Map Processor guarantees very legible characters and the greatest amount of picture detail possible
- Unmatched input compatibility with all analog and digital video sources and all computer graphics formats and electronic workstations up to 2,000 x 1,280 pixels
- Easy picture alignment
- Direct stacking
- Easy lamp and lens replacement
- Auto-source recognition and configuration
- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement of older generation projectors
- Up to 120 % off-axis projection and extra 25 % keystone correction

Technische Daten

BARCOREALITY 6400

Allgemeine technische Daten

Lichtausgabe	3400 ANSI Lumen
LCD-Panels	3 active matrix 1.8" diagonal S-XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1280x1024 pixels (5:4 aspect ratio)
Kompatibilität	All Current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV,...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic Workstations with a resolution up to 2000x1280 pixels/76 Hz Most sources with a pixel clock up to 200 MHz
Kontrast	> 250:1 (full white/full black) > 150:1 (5x4 checkerboard)
Lampe	A new 400 Watt metal-halide arc lamp pre-aligned for maximum light output with a typical lifetime of 1000 hours
Bildgröße	From 1-6 m, except for the QGD (0.8:1) lenses
Gewicht	Body only: 17.7 kg/39.0 lbs. Body + lens: 21-25 kg/46.3-55.1 lbs.

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.

www.barco.com

BARCO