


F70-4K8

4K UHD laser phosphor projector



- 4K UHD resolution
- Durable and robust for 24/7 operation
- High brightness
- Long lifetime (up to 60,000 hours)

The F70-4K8 is a laser phosphor projector with native WQXGA and up to 4K UHD resolution. The F70 series answers to the ProAV market's specific requirements - including high robustness, longer lifetime, and laser-sharp image quality. Projectors that do not meet these demands don't last long or might require frequent and expensive maintenance.

Thanks to its rugged design Barco's F70 is motion platform capable, making it the perfect choice for theme parks, dark rides and the most demanding fixed installations. With a lifetime of up to 60,000 hours (depending on the mode of operation), the F70 is one of the most durable projectors on the market and is ready for service in the most demanding environments.

Designed for 24/7 use

The F70 is designed for performance and reliability. Capable of running in any orientation, the F70 projectors offer more installation flexibility. All of Barco's F-series projectors feature the same high-resolution FLD and FLD+ lenses so that you can reuse your lenses.

Brighter, better

With brightness levels of 7,500 lumens, the F70-4K8 is one of the brightest single-chip DLP projectors on the market. With the Constant Light Output (CLO™) functionality, the projector produces constant brightness and color over a long period of time.

Product specifications**F70-4K8****General specifications**

| | |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Projector type | 1DLP laser phosphor |
| IR for NVG | no |
| Resolution | 3,840 x 2,400 (4K UHD) / 2,560 x 1,600 (native) |
| Brightness | 7,500 lumens |
| Brightness uniformity | 90% |
| Contrast ratio | 1800:1 sequential, 50,000:1 dynamic |
| Light source | Laser phosphor |
| Light source lifetime | Up to 60,000 hours, depending on mode of operation |
| Aspect ratio | 16:10 |
| Orientation | 360° rotation, no restrictions |
| Sealed DLP™ core | Yes |
| Color correction | P7 RealColor™ |
| CLO (constant light output) | Yes |
| Keystone correction | Yes |
| Image processing | Embedded warp & blend engine |
| 3D | Active stereoscopic 3D |
| Lens type | FLD/FLD+ |
| Optical lens shift | Vertical up to 146%, depending on lens Horizontal up to 70%, depending on lens Motorized zoom and focus (+ lens memory FLDX lenses) Motorized lens shift (with position memory on all lenses) |
| Inputs | HDSDI 2x DP1.2 2x dual link DVI-I HDBaseT HDMI™ 2.0 (HDCP2.2, HDR10) RJ 45 Ethernet DMX in/out RS232 in 2x USB 12v out |
| Input resolutions | Including and up to: 3,840 x 2,400 @ 60Hz 3,840 x 2,160 @ 60Hz 4,096 x 2,160 @ 60Hz 2,560 x 1,600 @ 120Hz refresh rates: 24Hz to 120Hz for WQXGA (2560x1600) and 24Hz to 60Hz for 4K/4KUHD (4096 x 2160/ 3860 x 2400) |
| Input color depth | DVI: Including and up to 2560x1600@60Hz 8 bit RGB and 3840x2400@50Hz 8 bit RGB DisplayPort: Including and up to 2560x1600@120Hz 12 bit RGB and 3840x2400@60Hz 8 bit RGB |
| Software tools | Projector Toolset |
| Control | IR, RS232, RJ45 |
| Network connection | IR, RS232, RJ45 |
| Power requirements | 100-240V / 50-60Hz |
| Power consumption | 1,100 W Max. |
| BTU per hour | Max 4,000 BTU/h |
| Noise level (typical at 25°C/77°F) | 36 dB(A) |
| Operating temperature | 10 -40 °C (sea level) |
| Operating humidity | 20 -80% RH |
| Storage temperature | -20 to 60 °C |
| Storage humidity | 10 -90% RH |
| Dimensions (WxLxH) | 475 x 593 x 286 mm (18,7 x 23,3 x 11,2 in) |
| Weight | 37 kg (81,5 lbs) |
| Standard accessories | Power cord, wireless remote control |
| Certifications | CE, FCC Class A and cCSAus |
| Warranty | Limited 5 years parts and labor, extendable |

Last updated: 09 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.