

SP4K-27HC

27,000 lumens flagship laser cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPureTM**
- **Fit and forget**

SP4K-27HC is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A custom-designed cinema projector with enhanced contrast for the ultimate image quality. The SP4K models come in many different configurations offering you the freedom of choice. Play with the available options to match your specific needs.

Brilliant image

The Series 4 brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The SP4K-27HC adds a 5000:1 extra high contrast for premium auditoriums. The Barco Active Image ManagementTM and its patented precision brightness technology guarantees flawless images with automatic white balances.

Ready for tomorrow, today

The Barco ColorgenicTM technology opens up more than 98.5% of Rec. 2020. SP4K-27HC is fully enabled for future innovations like 4K 120fps and HDR images. Deliver stunning results not only on day 1, but consistently throughout the lifetime of the product.

Barco EcoPureTM

This silent running projector (51dB(A)) is fully ready for boothless operation. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plateTM spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-27HC seamlessly integrates into your current setup.

Product specifications

SP4K-27HC

General specifications

| | |
|--------------------------------|--|
| Native brightness | 27,000 lumens (typical) |
| Native contrast ratio | 5000:1 (typical) |
| Digital MicroMirror Device™ | 3x 1.38" DC4K |
| Resolution | native 4K: 4096 x 2160 |
| Color gamut | DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates) |
| Light source | Laser |
| Prime lenses | 1.13-172; 1.35-1.84; 1.45-2.10; 1.65-2.70; 1.98-3.40 Very High-Contrast B-lenses |
| Long-term brightness stability | 40,000 hrs @ average usage conditions |
| Housing | integrated cooling design and patented sealed optical assembly |
| Dimensions (WxLxH) | projector incl. feet 760 x 1470 x 612 mm 29,92 x 57,54 x 24,09 inches |
| Weight | 170kg/375lbs |
| Power requirements | single phase or triple phase 200-240V 25A |
| Heat load (max. power) | 12,500 BTU/hr |
| Exhaust airflow | 615CFM |
| Ambient temperature | 40°C / 104F max. |
| Ambient humidity | 85% RH max. |
| Media server | Barco Alchemy ICMP-X and other media server brands ** supported |
| Power consumption | 3.9kW (3W in Eco mode) |
| Noise Level | 51dB(A) @1m and 25°C ambient temperature |
| 3D systems | Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported. |
| Safety requirements | Class 1 risk group 3 |
| User interface | Touch Display and/or web based |
| Notes | ** projector configuration with ICP-D; contact Barco service for the list of supported brands |

Last updated: 09 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.