

FL35 series

High-resolution LED DLP projector



- 100,000-hour LED lifetime
- Flexible installation orientation
- Active 3D stereo and 120 Hz refresh rate

Barco's FL35 projector has no lamp and no consumables and creates the world's most stunning image with a pixel precision of 2,560 x 1,600. Featuring 2nd generation LED illumination, the FL35 shows amazing pictures at double the resolution and 50 % more brightness than any other LED-illuminated projector, with an unmatched 100,000 hours lifetime . With its 2,560 x 1,600 native resolution, brightness level of up 1,000 ANSI lumens and 24/7 operation time - warranted for up to 5 years - the FL35 excels in image quality. The FL35 improves uptime and drastically reduces maintenance costs, operating costs, and technical resources.

Low Total Cost of Ownership

With no lamps, our 2nd generation patented solid-state ReaLED™ illumination provides up to 100,000 hours lifetime. The projector requires no re-calibration, no color degradation and no maintenance. This drastically improves your uptime while reducing operating costs and technical resources. Additionally, the FL35 has a low environmental footprint thanks to its low power consumption. The 2nd generation Solid State LED consumes up to 75% less power when compared to products of the same performance.

Unlimited installation flexibility

As it has no lamps, the FL35 can be placed in any orientation. With its comprehensive range of high-quality projection lenses, and industry standard mounting, it greatly simplifies installation. It features just one cabinet, complete with optics, I/O, processing, and control. The system's weight is only 16 kg (35 lbs.), including mounted lens. The rugged projector can easily be integrated onto motion platforms or in simple truss systems in any orientation angle.

Smooth imagery with Smear Reduction Processing™

Our unique frame rate processing and integrated adjustable SRP™ Smear Reduction Processing creates smooth imagery, perfect for fast-moving images.

- Up to 2,560 x 1,600 native pixel resolution
- Dual-link DVI input to produce more than 4 Megapixels
- 2nd Generation solid state ReaLED illumination
- Dual input capability up to 1,920 x 1,200
- 120 Hz refresh rate for smooth imagery
- Adjustable SRP™ smear reduction processing
- Adjustable brightness from 0-800 lumens, mode dependent (FL35 WQXGA)
- Adjustable brightness from 0-1000 lumens, mode dependent (FL35 WUXGA)
- Up to 100,000 hours service life
- Designed for 24/7 operation
- Designed for multi-channel systems
- Unique color matching capabilities with RealColor™
- Unrestricted installation flexibility
- Expandable and customizable I/O
- Wide range of Ultra high-quality projection lenses
- Compatible with X-PORT™ modules for increased connectivity options

Product specificaties

FL35 SERIES

General specifications

Concept	Single chip DLP, powered lens shift system.
Resolutie	WQXGA (2,560 x 1,600), WUXGA (1,920 x 1,200), 1080p (1,920 x 1,080)
Technologie	2nd Generation Solid State LED DLP® projector.
Helderheid	- Adjustable brightness from 0-800 lumens, mode dependent (FL35 WQXGA) - Adjustable brightness from 0-1000 lumens, mode dependent (FL35 WUXGA)
Contrast	Up to 8,000 : 1 (Infinite contrast and total black with Dynamic Black enabled)
Beeldverhouding	16:10 (WQXGA), 16:10 (WUXGA), 16:9 (1080p)
Beeldschermkleuren	30-bit
Latentie	~19 ms
Grafische indelingen computer	2,560 x 1,600 -640 x 480
Horizontale scanfrequenties	15 -150 kHz (resolution dependant)
Verticale scanfrequenties	48 -190 Hz (resolution dependant)
Videoformaten	HDTV (1080p, 1080i, 720p), EDTV (576p, 480p), SDTV (576i, 480i)
Lenswerking	Motorized zoom, Focus, Shift, Iris and Mechanical shutter
Beeldbreedte	0.5 -20 m
Lichtbron	LED
Levensduur lamp	Up to 100.000 hours
Computeringangen	2 x DVI-D, 1 x VGA, 2 x HDMI 1.3a, 1 x XPort1, 1 x XPort2
Video-ingang	2 x HDMI 1.3a, 1 x YPbPr, 1 x Component
Controlemogelijkheden	1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 2 x USB
Afmetingen	510 x 223 x 376 mm (WxHxD)
Gewicht	12.6 kg
Verzendingsafmetingen	520 x 370 x 780 mm (WxHxD)
Verzendgewicht af fabriek	20 kg
Voedingsvereisten	Certified rating: 8.4A, ~100-240V, 50-60Hz / Typical consumption: Max 325W@100V, ~2.7A, 50Hz; ~1.2A, 240V, 50Hz
Conformiteiten	CE, FCC Class A and cNus
Bedrijfstemperatuur	10 -40 °C
Opslagtemperatuur	-20 -60 °C
Hoogte	Up to 3,000 m
Vochtigheid in bedrijf	20 -80% RH
Vochtigheid bij opslag	10 -90% RH
Kleur	Black metallic
Garantie	Limited 3 years parts and labour. Up to 5 years total warranty available. Conditions apply.
Altijd beschikbare documentatie	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
MTBF	59,542 hours
BTU/uur	less than 1,100

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO