


MAAC-2123

多合一触控显示器



- 工作站和显示器合二为一
- 适合多种多样的模态应用程序
- 可选触摸屏，提供出色的用户体验

适合多种医疗环境中的图像采集

MAAC-2123 是为查看采集系统（包括移动和固定系统）中的多模态图像而设计的用户界面。这是一款 24 英寸的多合一设备，将工作站 (PC) 和显示器融合在一个机箱中，以便轻松操作。该设备采用纤薄的白色设计，可以轻松融入您的医疗环境。

灵活而放心的使用

该显示器符合 DICOM 标准，具备背光输出稳定功能和一致的图像质量，让您可以放心使用。MAAC-2123 提供极其强大的 CPU，适用于多种多样的模态应用程序。得益于该设备较长的生命周期，您可以在未来多年安心使用！

可选的触摸屏

MAAC-2123 5TW 可以为您提供带 P-Cap 多点触控屏幕和防眩光涂层玻璃的用户界面，从而实现出色的用户体验。MAAC-2123 5NW 是不带玻璃盖的非触摸版本。

MAAC-2123 附带 2 年的标准保修，您还可以通过我们的 ExtendedCare 服务延长保修期。如果您有任何问题，请随时与我们联系！

技术规格

MAAC-2123

显示器

屏幕技术	AHVA (IPS alike)
背光	WLED
活跃屏幕大小 (对角线)	23.8" (604.7mm)
活跃屏幕大小 (H x V)	527.04mm(H) x 296.46mm(V)
宽高比 (H:V)	16:09
分辨率	1920x1080 60Hz
彩色成像	Yes
像素大小	0.275mm x 0.275mm
响应时间	14ms
灰阶	16.7M colors (true 8 bits)
视角 (H, V)	178/178 degree (Typical)
亮度	400 nits (cd/m ²) (Typical); 320nits (Min.)
对比度	1000:1 (Typical)

系统规格

触摸屏	For Option: 5TW <ul style="list-style-type: none">Projected-Capacitive 10 points Multi Touch, USB interface.Surface Hardness: > 6H (P-CAP)
DICOM校准光源	<ul style="list-style-type: none">Light Sensor on the Rear Side of PanelBrightness for Calibration and Light sensor enable spec: 200 cd/m²
CPU	<ul style="list-style-type: none">6th Generation Intel® Core™ processorLGA 1151 socket type,Factory default: Intel® Core™ i5-6500TE Processor; 6M Cache, up to 3.30 GHz
冷却方式	Smart FAN design
图形	Integrated Intel® HD Graphics
环境光补偿 (ALC)	Preset values in OSD
电源	19V DC Input, 6.32A current rating, medical-grade 100V~240V 50/60Hz AC input power supply
功率消耗	45W (typ. WIN10 OS loaded only without peripherals connection) / 3W (stand-by)
存储容量	Two Removable 2.5" Storage bay with easy access mechanical lock design Factory default: 1 x 500G SATA HDD
系统内存	2 x DDR4-1866/ 2133 SO-DIMM socket, support up to 16GB capacity: Factory default: 1x DDR4 8GB Memory
操作系统	Windows® 10 LTSB 2016 64 bit

连通性

I/O端口	<ul style="list-style-type: none">5 x LAN Ports: All support PXE and WOL (Factory default PXE Disable)1 x Display Port (V1.2)1 x Reset push button1 x RS232 DB9 Male connector
USB端口	<ul style="list-style-type: none">4 x USB 2.0 type A female, stackable 2x2 connector2 x USB 3.0 type A female, stackable 1x2 connector1 x Mini USB for Scalar Board Firmware Update2 x USB 2.0 type A female on side panel

技术规格

MAAC-2123

音频	<ul style="list-style-type: none">▪ H110 embedded HDA, with ALC886 codec▪ No Internal Mic▪ 1 x Earphone Jack Support Mic-in / Stereo Audio-out on Bottom I/O▪ Integrated stereo speakers, 2 x 2Watt
配件	
固定	VESA 100 mm standard; Fixed with 4 screws on stand Stand screws: M4X14mm
功能	Height adjustable (100 mm +/-50 mm), tilt (-8° / +30°) and swivel (-45° / +45°), Pivot (portrait/ landscape; 90°)
符合	
认证	<ul style="list-style-type: none">▪ China RoHS▪ ROHS-2▪ REACH▪ WEEE
安全	<ul style="list-style-type: none">▪ CE safety (IEC 60601-1:2012 3.1 edition) and EMC (IEC 60601-1-2: 2014, EN 60601-1-2: 2015)▪ UL/cUL (ANSI/AAMI ES60601-1, CAN/SA-C22.2 No. 60601-1)▪ FCC (CFR47 part 15 Class B)▪ CCC (GB4943.1, GB9254, GB17625.1)
物理特性	
机械	Material: Plastic
防尘防水	IP 33 front (touch model only)
环境条件	
工作温度	0 ~ 35°C (Still Air)
存储 - 存储温度	-20 °C to 60 °C
存储湿度	20% -85% (non-condensing)
存储 - 运输湿度	5% to 85% (non-condensing)
操作压力	70 to 106 kPa
存储 - 运输压力	50 to 106 kPa

生成于: 18 Sep 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。