

D-Cine Premiere DP100

2k Digital Cinema projector for large screens up to 20m (65.6ft)



Especificaciones del producto

D-CINE PREMIERE DP100

Especificaciones generales	
Salida de luz	22,000 cinema lumens
Digital MicroMirror Device™	3 x 1.2" dark metal type Advanced DLP Cinema™ signal processing: CineCanvas™ image management; CinePalette™ color management, CineBlack™ contrast management and CineLink™ security management
resolución nativa	2048 x 1080
caja	Hermetically sealed DMD™ and optical assembly
ancho de pantalla	Screen width (screen gain 1.8) @ 14ftL: 25m -82ft adjustable light output CLO software
Montaje	Standing on pedestal, including caster & wheels Up to 15 degrees tilt on pedestal
lámpara	1.5k to 7k Xenon arc lamp sizes Compatible with standard and high performance lamp types
relación de contraste	2000:1
Entradas de video digital	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Objetivos primarios	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
Diagnósticos del proyector	Via touch screen Via D-Cine Communicator control software (theater edition delivered standard on every product) Via SNMP agent
Requisitos de alimentación	3 x 400V + N or 3 x 220V version available max. 29,250 BTU/hr (with 6.5kW lamp)
dimensiones	projector head: 640(H) x 730(W) x 1186(D) mm / 24.2(H) x 28.7(W) x 46.7(D) inch projector head + pedestal: 1466(H) x 730(W) x 1252(D) mm / 57.7(H) x 28.7(W) x 49.3(D) inch
peso	projector head + pedestal: approx. 205kg (452lb)
Opciones	- CLO -Constant Light Output control - Anamorphic lens fitting for 1.25:1 scope lens - Acsar 2 Alternative Content Input Processor - ImagePRO HD - SNMP agent (v3)
información de pedido	EU: R9010111 US: R9010118

Generado en: 09 Jul 2024

© 2024 Barco nv. Todos los derechos reservados. Prohibida la reproducción total o parcial sin autorización por escrito. Todos los nombres de marcas y de productos son marcas comerciales, marcas comerciales registradas o nombres comerciales de sus respectivos titulares. Debido a la innovación continua, la información y las especificaciones técnicas están sujetas a cambios sin previa notificación. Consulta www.barco.com para ver las especificaciones más recientes.

