

Versa® TUBE v3x

Linear LED tube for architectural applications



IP66
WATERPROOF



Product specifications**VERSA® TUBE V3X****General specifications**

Resolution	20 pixels/meter
Color depth	48-bit
Refresh rate	>1000 Hz
Viewing angle	180° linear x 270° radial
Brightness	1,500 cd/m2 (nits) calibrated
Calibration	D65
Interconnection	Barco's custom integrated AC power & data connector
Power	100 -240VAC, 50/60Hz, auto-sensing, auto-switching
Power consumption	44W
Temperature range	-20° to 50°C
Length	1.0m
MTBF	50,000 hours @ 50°C ambient @ 20% load 10,000 hours @ 40°C ambient @ 100% load
Weather rating	IP66

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.